


OGA DIAGONAL: 21.36 [542.51]
VA DIAGONAL: 20.65 [524.39]
PA DIAGONAL: 19.46 [494.24]

TOP LEVEL NUMBER	US NUMBER	TYPE	DM A	TOTAL (GAS TO CONNECTOR)	A/G FINISH	PROD SPEC
17-9261-205	98-0003-2721-7	FFC	8.00"	[203.20]	AG500	23655
17-9261-227	98-0003-2724-1	SER	8.00"	[203.20]	AG500	23655
17-9261-206	98-0003-2722-5	NOV	SEE DWG		AG500	23655
17-9261-226	98-0003-3047-6	USB R	8.00"	[203.20]	AG500	23655
N/A	98-0003-3536-8	HID D	8.00"	[203.20]	AG500	23655
N/A	98-1100-0105-8	FFC	8.00"	[203.20]	WC100	34523
N/A	98-1100-0106-6	USB R	8.00"	[203.20]	WC100	34523



NOTES:

1. WEIGHT OF GLASS IN GRAMS: 1062±10%
2. NICOMATIC HOUSING P/N: OLO5
NICOMATIC RECEPTACLES (PINS) MATTE TIN PLATED P/N: 14106-12
HOUSING ORIENTED WITH LATCH DOWN

PINOUT	
1	UL
2	UR
3	SHL
4	LR
5	LL

UNITS INCHES [MM]		3M TOUCH SYSTEMS METHUEN, MA USA		TITLE		CHANGE NOTICE		DATE		DRAWN	
TOLERANCES UNLESS OTHERWISE SPECIFIED				MARKETING DRAWING SCT32NN 20.65" W							
.X ± .XX ±.03 [.76] .XXX ±.015 [.38] ANGLES ±1°		©COPYRIGHT 2004 THIS DOCUMENT IS COPYRIGHTED PROPERTY OF THE 3M COMPANY AND MAY NOT BE REPRODUCED WITHOUT 3M WRITTEN PERMISSION OR USED OR DISCLOSED FOR OTHER THAN 3M AUTHORIZED PURPOSES.									
THIRD ANGLE PROJECTION				DRAWN		MTD		9/7/06			
DO NOT SCALE DRAWING				CAD FORMAT		AUTOCAD		SHEET		1 OF 1	
SCALE 1 = 1				SIZE		C		DOCUMENT NO.		TSD-32744	
								REV		K	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

3M:

[98-0003-2721-7](#) [98-0003-2724-1](#) [98-0003-3047-6](#)