



OGA DIAGONAL: 19.32 [490.72]
VA DIAGONAL: 18.61 [472.77]
PA DIAGONAL: 17.54 [445.57]

TOP LEVEL NUMBER	US NUMBER	TYPE	DIM "A" (TOTAL GLASS TO CONNECTOR)	A/G FINISH	PROD SPEC
17-9591-205	98-0003-2274-7	FFC	8.00" [203.20]	AG500	23655
17-9591-226	98-0003-3265-4	USB R	8.00" [203.20]	AG500	23655
17-9591-227	98-0003-3266-2	SER	8.00" [203.20]	AG500	23655
N/A	98-1100-0099-3	FFC	8.00" [203.20]	WC100	34523
N/A	98-1100-0100-9	USB R	8.00" [203.20]	WC100	34523



NOTES:

1. WEIGHT OF GLASS IN GRAMS: 825±10%
HOUSING ORIENTED WITH LATCH DOWN

PINOUT	
1	UL
2	UR
3	SHLD
4	LR
5	LL

UNITS	INCHES [MM]
TOLERANCES UNLESS OTHERWISE SPECIFIED	
.X	± .03 [.76]
.XX	± .015 [.38]
.XXX	± .01 [.25]
ANGLES	± 1°
THIRD ANGLE PROJECTION	
DO NOT SCALE DRAWING	
SCALE	1 = 1

3M	3M TOUCH SYSTEMS METHUEN, MA USA
© COPYRIGHT 2004 THIS DOCUMENT IS COPYRIGHTED PROPERTY OF THE 3M COMPANY AND MAY NOT BE REPRODUCED WITHOUT 3M WRITTEN PERMISSION OR USED OR DISCLOSED FOR OTHER THAN 3M AUTHORIZED PURPOSES.	
DRAWN	S.Berard 10/09/08

REV	REVISION	DATE	SB
F	REVISED PER CO 036100	2/13	SB
CHANGE NOTICE			
TITLE			
MARKETING DRAWING SCT32NN 18.61" W			
CAD FORMAT		SHEET	
AUTOCAD		1 OF 1	
SIZE	DOCUMENT NO.	REV	
C	TSD-36237	F	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

3M:

[98-0003-2274-7](#) [98-0003-3265-4](#) [98-0003-3266-2](#)