



Product Description

3M™ Troubleshooter™ Baseboard Stripper is a ready-to-use, heavy-duty cleaner packaged in an aerosol container. It is designed to remove heavy soils, wax and floor finish buildup from hard surfaces.

Special Features

- Thick white foam clings to vertical surfaces and resists dripping
- Aggressive formula penetrates and loosens buildup quickly and thoroughly

Applications

- For use on baseboards, floor edges, corners, stairways and ceramic tile
- Convenient aerosol spray can be used in tough-to-reach areas

Note: Not for use on painted surfaces or old asphalt tile – immediately wipe off any overspray.

Quick Links

[Resource Library](#)
[Safety Data Sheets \(SDS\)](#)
[Video Library](#)

Some of these links lead to web-based resources that are not product-specific.

Packaging and Marking

21-ounce aerosol can – 12 cans per case

General Use Directions

1. Shake can well.
2. Hold can upside down and spray 6-10 inches from surface. Cover the soiled area with a thin, even coat.
3. If any overspray onto other surfaces occurs, wipe off immediately.
4. Wait 3-5 minutes (or longer where there is severe buildup).
5. Wet-scrub the surface using a 3M™ Doodlebug™ Pad Holder 6472 fitted with a 3M™ Doodlebug™ Brown Scrub 'n Strip Pad 8541, 3M™ Doodlebug™ Hi Pro Pad 8550, or a similar product.
6. For uneven surfaces (e.g., grout, brick or door jambs), use a 3M™ General Purpose Brush 4020 with a 3M™ Doodlebug™ Handblock Pad Holder 6473.
7. Rinse surface with clean warm water.

Note: Prior to use, clean a small, inconspicuous area. Note any change in color or texture, particularly on old tile floors. Do not apply to painted surfaces. If unacceptable abrasion or scratching occurs, use a less aggressive pad.

Note: Refer to product Safety Data Sheet SDS 10-2818-2 for specific health hazard, first aid and precautionary information.

3M™ Troubleshooter™ Baseboard Stripper (Aerosol)

Precautionary Summary

Do not use on soft metal and plastic surfaces, painted surfaces, or other surfaces that are easily scratched.

Health and Safety

When handling any chemical products, read the manufacturers' container labels and the Safety Data Sheets (SDS) for important health, safety and environmental information. To obtain SDS sheets for 3M products, go to 3M.com/SDS, or by mail; or in case of an emergency, call 1-888-364-3577 or 1-651-737-6501. When using any equipment, always follow the manufacturers' instructions for safe operation.

Technical Information

Technical information and data, recommendations, and other statements provided by 3M are based on information, tests, or experience which 3M believes to be reliable, but the accuracy or completeness of such information is not guaranteed. Such technical information and data are intended for persons with knowledge and technical skills sufficient to assess and apply their own informed judgment to the information. The typical values shown should not be used for the purpose of specification limits. If you have questions about this Product, contact the **Customer Service Department at 1-800-852-9722**.

Product Use

Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. Given the variety of factors that can affect the use and performance of a 3M product, user is solely responsible for evaluating the 3M product and determining whether it is fit for a particular purpose and suitable for user's method of application.

Warranty

3M warrants that each 3M product will be free from defects in material and manufacture for 90 days from the date of purchase from 3M's authorized distributor. 3M MAKES NO OTHER EXPRESS OR IMPLIED WARRANTIES, INCLUDING ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE.

Limited Remedy

If a 3M product does not conform to this warranty, the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

No Extension of Warranty

In the case of an approved warranty claim, the replacement Product will carry only the remaining term of the original warranty period.

Limitation of Liability

Except where prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted.

Anchorage

11151 Calaska Circle
Anchorage, AK 99515
Telephone: 907-522-5200
Facsimile 907-522-1645

Honolulu

4443 Malaai Street
Honolulu, HI 96818
Mail to: P.O. Box 30048
Honolulu, HI 96820
Telephone: 808-422-2721
Facsimile 808-422-9557

Continental United States

Customer Service Department
3M Center Building 223-5S-07
St. Paul, MN 55144-1000
Order Entry 1-800-852-9722
Facsimile 1-800-447-0408

3M Canada

1840 Oxford Street East
London, Ontario, Canada
N5V 3G2
Mail to: P.O. Box 5757
London, Ontario, Canada
N6A 4T1
Telephone: 800-364-3577
Facsimile: 800-479-4453

Commercial Solutions Division

3M Center, Building 220-12E-04
St. Paul, MN 55144

1-800-328-0033
3M.com/Facility

© 3M 2018. All rights reserved.
3M, Doodlebug and TroubleShooter are trademarks of 3M Company.
Used under license in Canada.
All other trademarks are property of their respective owners. Revision
A, June 2018. Please recycle.
60142



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

3M:

[7100134190](#)