

3M

Vinyl Duct Tape

3903

Technical Data

January, 2018

Product Description 3M™ Vinyl Duct Tape 3903 is a general purpose duct tape with a rubber adhesive and hand tearable, embossed vinyl backing.

| Product Construction | Backing | Adhesive | Colors | Standard Roll Length |
|----------------------|----------------|----------|--|----------------------|
| | Embossed Vinyl | Rubber | Black, Blue, Green, Gray, Red, White, Yellow | 50 yds. (45.7 m) |

Typical Physical Properties Note: The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

| | | ASTM Test Method |
|------------------------|------------------------------------|------------------|
| Adhesion to Steel: | 15.4 oz./in. width (16.8 N/100 mm) | D-3330 |
| Tensile Strength: | 14.5 lbs./in. width (253 N/100 mm) | D-3759 |
| Elongation at Break: | 134% | D-3759 |
| Tape Thickness: | 7.3 mils (0.19 mm) | D-3652 |
| Temperature Use Range: | Up to 200°F (93°C) | |

Features

- Embossed vinyl backing is conformable to many surfaces.
- Hand-tearable.
- Rubber adhesive bonds well to many surfaces.

Application Ideas

- Applications in the construction, electrical and industrial markets.
- Applications for identification and protection.
- Sealing and protecting surfaces and openings from dust, dirt and moisture.
- Color-coding, non-critical masking, wrapping and bundling.

3M™ Vinyl Duct Tape 3903

| | |
|--|---|
| Storage | Store under normal conditions of 70°F (21°C) and 50% R.H. in the original carton. |
| Shelf Life | To obtain best performance, use this product within 12 months from date of manufacture. |
| Technical Information | The technical information, guidance, and other statements contained in this document or otherwise provided by 3M are based upon records, tests, or experience that 3M believes to be reliable, but the accuracy, completeness, and representative nature of such information is not guaranteed. Such information is intended for people with knowledge and technical skills sufficient to assess and apply their own informed judgment to the information. No license under any 3M or third party intellectual property rights is granted or implied with this information. |
| Product Selection and Use | Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. As a result, customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customer's application, including conducting a workplace hazard assessment and reviewing all applicable regulations and standards (e.g., OSHA, ANSI, etc.). Failure to properly evaluate, select, and use a 3M product and appropriate safety products, or to meet all applicable safety regulations, may result in injury, sickness, death, and/or harm to property. |
| Warranty, Limited Remedy, and Disclaimer | Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature (in which case such warranty governs), 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE. If a 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price. |
| Limitation of Liability | Except for the limited remedy stated above, and except to the extent prohibited by law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability. |



This Industrial Adhesives and Tapes Division product was manufactured under a 3M quality system registered to ISO 9001 standards.



Industrial Adhesives and Tapes Division
3M Center, Building 225-3S-06
St. Paul, MN 55144-1000
800-362-3550 • 877-369-2923 (Fax)
www.3M.com/industrial

3M is a trademark of 3M Company. Printed in U.S.A.
©3M 2018 E70-0709-4664-8 (11/10)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

3M:

7100145925