



1139 Electrical Tape

Polyester Film/Glass Filament Reinforced Tape with Acrylic Pressure-Sensitive Adhesive

Data Sheet



Product Description

3M™ 1139 Tape is a 6.5 mil polyester film/glass filament tape coated with an acrylic, pressure-sensitive adhesive.

- UL Recognized, Class F (155°C)
- Solvent resistant without thermosetting
- High breaking strength
- Suitable for heavy duty use

Applications

3M 1139 tape is especially suited for heavy duty air and oil filled transfer applications, reinforcements, holding and separating ground insulation, bundling motor coils and coil covering.

UL Component Recognition

- Temperature not exceeding 155°C

UL File Number E17385 A and B, Guide OANZ2. Underwriters Laboratories (UL) Recognized products have been evaluated for use as components of end-product equipment that is listed or classified by UL. To achieve Underwriters Laboratories recognition, component construction must meet UL specifications and conditions of acceptability for proper and safe use of the component or product.

Typical Properties

Typical Values

Adhesive	Acrylic
Backing	Polyester film/Glass filament
Backing Thickness	5.5 mils (0.140mm)
Total Thickness ¹	6.5 mils (0.165 mm)
Color	Clear
Temperature Class	155°C
Dielectric Breakdown ¹	5500V
Breaking Strength ¹	225 lbs/in (394N/10mm)
Elongation ¹ (% at break)	6%
Adhesion to Steel ¹	35 oz/in (3.85N/10mm)

Note: Typical properties are not recommended for specification purposes. Product specifications will be provided upon request.

3M is a trademark of 3M

IMPORTANT NOTICE

Before using this product, you must evaluate it and determine if it is suitable for your intended application. You assume all risks and liability associated with such use.

Warranty; Limited Remedy; Limited Liability. This product will be free from defects in material and manufacture as of the date of purchase. **3M MAKES NO OTHER WARRANTIES INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE.** If this product is defective within the warranty period stated above, your exclusive remedy shall be, at 3M's option, to replace or repair the 3M product or refund the purchase price of the 3M product. **Except where prohibited by law, 3M will not be liable for any loss or damage arising from this 3M product, whether direct, indirect, special, incidental or consequential regardless of the legal theory asserted.**



Electrical Products Division

6801 River Place Blvd.
Austin, TX 78726-9000
<http://www.3M.com/elpd/oem>

Litho in USA.
© 3M IPC 2001 78-8125-9947-6-B

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

3M:
7010349213