




ScotchlokTM Terminals

MVU18-180DM-A, MVU14-180DM-A,
Male Snap Plug, Vinyl Insulated,
Butted Seam



Data Sheet

March 2008

Product Number	Wire Range (AWG)	Mating Snap Diameter S	L	Maximum Insulation Diameter
MVU18-180DM-A	22-18	0.180	.83	.15
MVU14-180DM-A	16-14	0.180	.83	.17

Specifications

Wire Size:	See Table Above
Barrel Seam:	Butted
Maximum Voltage Rating:	300 V Building Wire
Maximum Operating Temp:	167°F (75°C)
Maximum Current:	Same as Wire
Insulator Material:	Vinyl
Terminal Material:	Brass
Terminal Plating:	Tin

Installation Information

WARNING

Turn power off before installing or removing terminal. All electrical work should be done according to appropriate electrical codes.

Strip away the end 3/8 inch of wire insulation.

Make the crimp in the proper station of a recommended 3MTM ScotchlokTM Crimp Tool: TH-440, TH-450.



Barrel Crimp (Electrical)

Engineering Specification

Crimp-Type Snap Plug Connectors shall, electrically and mechanically, connect permanently to a pre-stripped end of a stranded copper wire, and have a round tongue portion for mating to a Snap Receptacle in a separable, reusable manner.

The connector line shall offer tongue variations sized to grip male tabs 0.156" and 0.180" diameter and barrel variations in wire (AWG) size (22-18, 16-14, 12-10) and construction (vinyl insulated, nylon insulated with insulation grip).

The separable connector formed by a paired Male Snap Plug and Female Snap Receptacle may require a suitable strain relief to prevent accidental separation.

Important Notice

All statements, technical information, and recommendations related to 3M's products are based on information believed to be reliable, but the accuracy or completeness is not guaranteed. Before using this product, you must evaluate it and determine if it is suitable for your intended application. You assume all risks and liability associated with such use. Any statements related to the product which are not contained in 3M's current publications, or any contrary statements contained on your purchase order shall have no force or effect unless expressly agreed upon, in writing, by an authorized officer of 3M.

Warranty; Limited Remedy; Limited Liability:

This product will be free from defects in material and manufacture at the time of purchase. **3M MAKES NO OTHER WARRANTIES INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE.** If this product is defective within the warranty period stated above, your exclusive remedy shall be, at 3M's option, to replace or repair the 3M product or refund the purchase price of the 3M product. **Except where prohibited by law, 3M will not be liable for any indirect, special, incidental or consequential loss or damage arising from this 3M product, regardless of the legal theory asserted.**

3M and Scotchlok are trademarks of 3M Company.



Electrical Markets Division

6801 River Place Blvd.
Austin, TX 78726-9000
800 245 3573
FAX 800 245 0329
www.3M.com/electrical

Please recycle.
© 3M 2008 All rights reserved.
78-8127-6876-6_A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

3M:

[MVU18-180DMK-A](#) [MVU14-180DMK-A](#)