


Male Disconnects – Non-Insulated Butted Seam



Product Number†	UPC (054007-)	Wire Range (AWG)	Male Tab Width (W) x Thickness	L	Barrel Length	Barrel I.D.	Terminals per:	
							Carton	Case
MU18-187DMK	02372	22-18	0.187 x 0.020	0.64	0.24	0.080	—	1000
MU18-250DMK	02364	22-18	0.250 x 0.032	0.73	0.25	0.065	—	1000
MU14-187DMK	01783	16-14	0.187 x 0.020	0.64	0.24	0.080	—	1000
MU14-250DMX	22971	16-14	0.250 x 0.032	0.73	0.25	0.085	100	500
MU14-250DMK	01784	16-14	0.250 x 0.032	0.73	0.25	0.085	—	1000
MU10-250DMX	23912	12-10	0.250 x 0.032	0.75	0.25	0.150	100	500
MU10-250DMK	02056	12-10	0.250 x 0.032	0.75	0.25	0.150	—	500



Wire Range
Suggested Mate

MU18-187DM
22-18
MU18-187DF

MU18-250DM
22-18
MU18-250DF

MU14-187DM
16-14
MU14-187DF

MU14-250DM
16-14
MU14-250DF

MU10-250DM
12-10
MU10-250DF

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

3M:

[MU10-250DMK](#) [MU14-250DMK](#) [MU14-187DMK](#) [MU18-250DMK](#)