


1. SPECIFICATIONS

AMF-O60G42-3CWH2-IP67

01	Electret's Type	Foil type
02	Sensitivity	-42±3dB (0dB=1V/Pa,1KHz)
03	Standard Operation Voltage	2.0 V
04	Output Impedance	2.2 KΩ
05	Directivity	Omni directional
06	Frequency Range	100 - 10K Hz
07	Max. Operation Voltage	10V
08	Current Consumption	Max.0.5mA
09	Sensitivity Reduction	Within -3dB 0dB=1V/Pa,1KHz Vs=2.0to 1.5V
10	S/N Ratio	≥58dB
11	Sound Pressure Level	110 dB
12	Operating Temperature	-20~+60°C
13	Storage Temperature	-25~+70°C

REV NO.	REVISION NOTE	APPROVAL	DATE
---------	---------------	----------	------



RoHS

TITLE: MICROPHONE		DRAWN: <i>Jack</i>	2018/05/09	SCALE: 5:1	SHEET: 1 of 1
PART NO. AMB-060G42-3CWH2-IP67	1	DESIGNED: R & D OF AAT		UNITS: mm	
		CHECKED:		TOLERANCE ± 0.3	
DWG NO. B6022AL-SDN-D110-M	REV	APPROVAL:		UNLESS OTHERWISE SPECIFIED:	
		MATERIAL: AL		ONE PLACE DECIMAL ± *** TWO PLACE DECIMAL ± *** THREE PLACE DECIMAL ± ***	



ADVANCED ACOUSTIC TECHNOLOGY CORPORATION

For more information, please contact AATC.

AATC

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

AATC:

[AMB-O60G42-3CWH2-IP67](#)