



1. SPECIFICATION

AC-1612C-1P

ITEM		UNITS	SPECIFICATIONS	CONDITIONS
01	Rated Voltage	V	12	 Standard state, standard drive circuit. Square wave 1/2 duty.
02	Operating Voltage	V	9 ~ 15	
03	Consumption Current	mA Max.	50	
04	Sound pressure level (Distance at 10cm)	dB(A) Min.	92	Rated voltage, rated frequency.
05	Direct Current Resistance	Ω	115 ± 12	
06	Rated Frequency	Hz	2800	

REV NO.	REVISION NOTE	APPROVAL	DATE
---------	---------------	----------	------



RoHS

TITLE: ELECTRO MAGNETIC BUZZER		DRAWN: Zack	2018/05/17	SCALE: 4:1	SHEET: 1 of 1
PART NO. AC-1612C-1P		DESIGNED: R&D OF AAT		UNITS: mm	
DWG NO. UGCM1612AP5.0H-92		CHECKED:		TOLERANCE ± 0.5	
		APPROVAL:		UNLESS OTHERWISE SPECIFIED:	
		MATERIAL: NORYL		ONE PLACE DECIMAL \pm ***	
				TWO PLACE DECIMAL \pm ***	
				THREE PLACE DECIMAL \pm ***	



ADVANCED ACOUSTIC TECHNOLOGY CORPORATION

For more information, please contact AATC.

AATC

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[AATC:](#)

[AC-1612C-1P](#)