


1. SPECIFICATION

AC-1205G-HF

ITEM		UNITS	SPECIFICATIONS	CONDITIONS
01	Rated Voltage	V	5	 Standard state, standard drive circuit. Square wave 1/2 duty.
02	Operating Voltage	V	3 ~ 8	
03	Consumption Current	mA Max.	50	
04	Sound pressure level (Distance at 10cm )	dB(A) Min.	85	Rated voltage, rated frequency.
05	Direct Current Resistance	Ω	40±6	
06	Rated Frequency	Hz	2400	

REV NO.


REVISION NOTE

APPROVAL


DATE

NO LABEL


U0712

WEEK  
YEAR  
LINE


Sound Hole ø2.3



Potting



# RECOMMEND PCB LAYOUT



## PART NO. DESCRIPTION.

A : COMPANY NAME  
 C : MAGNETIC BUZZER  
 |  
 12 : DIAMETER  
 05 : VOLTAGE  
 G : RESISTANCE 40 ohm  
 |  
 HF : NO Halogen

HF

TITLE: MAGNETIC BUZZER

DRAWN: Hank 2020/02/15

SCALE: 3:1 SHEET: 1 OF 1

PART NO. AC-1205G-HF

DESIGNED: R&amp;D OF AAT

UNITS: mm

CHECKED:

TOLERANCE ± 0.5

DWG NO.

APPROVAL:

UNLESS OTHERWISE SPECIFIED:

ONE PLACE DECIMAL ± \*\*\*

REV

MATERIAL: PBT

TWO PLACE DECIMAL ± \*\*\*

THREE PLACE DECIMAL ± \*\*\*



ADVANCED ACOUSTIC TECHNOLOGY CORPORATION

For more information, please contact AATC.

AATC

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[AATC:](#)

[AC-1205G-HF](#)