



1. SPECIFICATION

AC-703R-P4

ITEM		UNITS	SPECIFICATIONS	CONDITIONS
01	Rated Voltage	V	3	
02	Operating Voltage	V	2 ~ 4	
03	Consumption Current	mA (Max)	Mean : 150	Applying rated voltage, rated frequency Square wave, 1/2 duty subject to standard state.
			Peak : 450	
04	Direct Current Resistance	Ω	8 ± 2	
05	Sound pressure level (Distance at 10cm)	dBA (Min)	70	Applying rated voltage, rated frequency Square wave, 1/2 duty subject to standard state.
06	Rated Frequency	Hz	2700	

REV NO.	REVISION NOTE	APPROVAL	DATE
---------	---------------	----------	------



RoHS

TITLE: ELECTRO MAGNETIC BUZZER		DRAWN: Zack	2012/12/27	SCALE: 4:1	SHEET: 1 of 1
PART NO. AC-703R-P4	1	DESIGNED: R&D OF AAT		UNITS: mm	
DWG NO. AC-703R-P4		CHECKED:		TOLERANCE ± 0.5	
		APPROVAL:		UNLESS OTHERWISE SPECIFIED:	
	REV	MATERIAL: PBT		ONE PLACE DECIMAL ± ***	
				TWO PLACE DECIMAL ± ***	
				THREE PLACE DECIMAL ± ***	



ADVANCED ACOUSTIC TECHNOLOGY CORPORATION

For more information, please contact AATC.

AATC

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[AATC:](#)

[AC-703R-P4](#)