

1. SPECIFICATION

AK-10210208HC-1

ITEM		SPECIFICATIONS	
01	Type	Dynamic speaker	
02	Dimension	External diameter 102 x 102 mm	
03	Rated Input Power	10 W	
04	Max. Input Power	20 W for 1 minute	
05	Impedance	8 Ω ± 15% at 0.8KHz 1V	
06	Resonance Frequency (Fo)	180 Hz ± 20% at Fo, 1V	
07	Sound pressure level	86 dB(10W/1.0M) ± 3 dB	at AVE 0.5, 0.8, 1.0, 1.2 KHz.
		93 dB(10W/0.5M) ± 3 dB	
08	Frequency Range	Fo – 8 K Hz	
09	Total Harmonics Distortion	Max 10 % at 1 KHz, 1.5V.	

ADVANCED ACOUSTIC TECHNOLOGY CORPORATION

For more information, please contact AATC.

AATC

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

AATC:

[AK-10210208HC-1](#)