


1. SPECIFICATION

AE-1558E-WE

TYPE		EXTERNAL -drive type sound element		
ITEM		UNITS	SPECIFICATIONS	CONDITIONS
01	Input Voltage	V (Max)	30	Vp-p (Square Wave) 1/2 duty
02	Resonant Frequency	KHz	5.8 ± 0.5	at 25± 2℃ , 45~60% RH
03	Resonant Impedance	Ω (Max)	300	at 25± 2℃ , 45~60% RH
04	Capacitance	pF	100000±30%	At 100Hz
05	Plate Material			BRASS



Wire: UL1571,32AWG

RoHS

For more information, please contact AATC.

AATC

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[AATC:](#)

[AE-1558E-WE](#)