


1. SPECIFICATION

AKR-35200820-PPC-1C

ITEM		SPECIFICATIONS	
01	Type	Dynamic Speaker	
02	Dimension	External diameter 35 x 20 mm	
03	Rated Input Power	2.0 W	
04	Max. Input Power	3.0 W for 1 minute	
05	Impedance	$8\Omega \pm 15\%$ at 1KHz 1V	
06	Resonance Frequency (Fo)	850 Hz $\pm 20\%$ at Fo, 1V	
07	Sound pressure level	97 dB(2.0W/0.1M) ± 3 dB	at AVE 1.0, 1.2, 1.4, 1.5 KHz.
08	Frequency Range	Fo – 10 K Hz	
09	Total Harmonics Distortion	Max 10 % at 1 KHz, 1.0 W.	

REV NO.	REVISION NOTE	APPROVAL	DATE
---------	---------------	----------	------



WIRE: UL1571,AWG24# 併線
CONNECTOR: Equivalent to JST PHR-4

RoHS

TITLE: DYNAMIC SPEAKER		DRAWN: Zack		2016/04/29	SCALE: 1:1	SHEET: 1 : 1
PART NO. AKR-35200820-PPC-1C	2	DESIGNED: R & D OF AAT			UNITS: mm	
		CHECKED:			TOLERANCE ± 0.5	
DWG NO. CXS2035076LP120/50-R08W2.0-F	REV	APPROVAL:			UNLESS OTHERWISE SPECIFIED.	
		MATERIAL: ABS			ONE PLACE DECIMAL ± ***	
					TWO PLACE DECIMAL ± ***	
					THREE PLACE DECIMAL ± ***	



ADVANCED ACOUSTIC TECHNOLOGY CORPORATION

For more information, please contact AATC.

AATC

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

AATC:

[AKR-35200820-PPC-1](#)