

1. SPECIFICATION

ART-38150H-PP-1P




	ITEM	UNIT	SPECIFICATIONS	CONDITION
01	Dimension 尺寸	mm	Φ 38 X 21	Refer to attached drawing in details.
02	Input power 輸入功率	mW	1	White noise is applied for 96 hours.
03	Max. Input power 額定輸入最大功率	mW	Max.10	at room temperature for 60s on and 120s off for 10 cycles.
04	Impedance 交流阻抗	Ω	150 ±15%	at 1KHz /1V.
05	S.P.L 音壓位準 Sound pressure level	dB	94 ±3	at 1KHz 60mV with IEC318 coupler.
06	Frequency range 有效頻寬	Hz	300~3.4K	
07	T.H.D 總諧波失真 Total Harmonics Distortion	%	Max.5	at 1KHz 387mV/1mW Input power.

REV NO.

REVISION NOTE

APPROVAL

DATE



RoHS

TITLE: DYNAMIC RECEIVER

DRAWN: Moose 2016/04/28

SCALE: 1:1

SHEET: 1:1

PART NO. CXR38210-R150-HA

DESIGNED: R&D OF AAT

UNITS: mm

CHECKED:

TOLERANCE ± 0.5

APPROVAL:

UNLESS OTHERWISE SPECIFIED:

ONE PLACE DECIMAL ± ***

TWO PLACE DECIMAL ± ***

THREE PLACE DECIMAL ± ***

DWG NO. ART-38150H-PP-1P

REV

MATERIAL: ****



ADVANCED ACOUSTIC TECHNOLOGY CORPORATION

For more information, please contact AATC.

AATC

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

AATC:

[ART-38150H-PP-1P](#)