


1. SPECIFICATION

AKR-15110807-PAM-5CV

ITEM		SPECIFICATIONS	
01	Type	Dynamic Speaker	
02	Dimension	External diameter 15 x 11 mm	
03	Rated Input Power	0.7 W	
04	Max. Input Power	1.0 W for 1 minute	
05	Impedance	$8\Omega \pm 15\%$ at 2 KHz 2V	
06	Resonance Frequency (Fo)	700 Hz $\pm 20\%$ at Fo, 1V	
07	Sound pressure level	88 dB(0.7W/0.1M) ± 3 dB	at AVE 0.8, 1.0, 1.5, 2.0 KHz.
08	Frequency Range	Fo – 20 K Hz	
09	Total Harmonics Distortion	Max 10 % at 1 KHz, 0.89V.	

REV NO.	REVISION NOTE	APPROVAL	DATE
---------	---------------	----------	------



WIRE:UL1007 28#AWG
Connector:Equivalent to JST PHR-2

RoHS

TITLE: DYNAMIC SPEAKER		DRAWN: Sunny 2018-5-24	SCALE: 1:1	SHEET: 1 : 1
PART NO. AKR-15110807-PAM-5CV	1 REV	DESIGNED: R & D OF AAT	UNITS: mm	TOLERANCE ± 0.5
DWG NO. UGSP111508-18GC200-02		CHECKED:	UNLESS OTHERWISE SPECIFIED:	
		APPROVAL:	ONE PLACE DECIMAL ± ***	
		MATERIAL: PBT+SUS	TWO PLACE DECIMAL ± ***	
			THREE PLACE DECIMAL ± ***	



ADVANCED ACOUSTIC TECHNOLOGY CORPORATION

For more information, please contact AATC.

AATC

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

AATC:

[AKR-15110807-PAM-5CV](#)