

## 1. SPECIFICATION

AK-402008CC-6C7 (RoHS)

| ITEM |                            | SPECIFICATIONS             |                            |
|------|----------------------------|----------------------------|----------------------------|
| 01   | Type                       | Dynamic speaker            |                            |
| 02   | Dimension                  | External diameter 40X20mm  |                            |
| 03   | Rated Input Power          | 2.0 W                      |                            |
| 04   | Max. Input Power           | 3.0 W    for 1 minute      |                            |
| 05   | Impedance                  | 8Ω ± 15% at    1 KHz    1V |                            |
| 06   | Resonance Frequency (Fo)   | 400 Hz ± 20% at Fo, 1V     |                            |
| 07   | Sensitivity (S.P.L.)       | 72 dB(1.0W/1.0M) ± 3 dB    | at AVE 0.6,0.8,1.0,1.2KHz. |
|      |                            | 95 dB(2.0W/0.1M) ± 3 dB    |                            |
| 08   | Frequency Range            | Fo – 2.2 K Hz              |                            |
| 09   | Total Harmonics Distortion | Max 10 % at 1 KHz, 1.5V.   |                            |



For more information, please contact AATC.

AATC

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

AATC:

[AK-402008CC-6C7](#)