




1. SPECIFICATION

ADI-F10H5C

ITEM		UNITS	SPECIFICATIONS	CONDITIONS
01	Rated Voltage	V	5.0	
02	Operating Voltage	V	4.0 ~ 7.0	
03	Consumption Current	mA (Max)	30	Rated Voltage
04	Resonant Frequency	Hz	2700 ± 200	Rated Voltage
05	Response times	ms	≥ 100	
06	Sound pressure level	dB(A) Min.	85	Distance at 10cm Rated Voltage / Resonant Frequency
07	Operating Temp.	℃	-30 ~ +70	
08	Storage Temp.	℃	-40 ~ +85	
09	Weight	g	0.6±0.2	

REV NO.	REVISION NOTE	APPROVAL	DATE
---------	---------------	----------	------



RoHS

TITLE: SOUND TRANSDUCER (SMD)		DRAWN: Hank	2020/05/08	SCALE: 1:1	SHEET: 1 : 1
PART NO.	ADI-F10H5C	DESIGNED:	R & D OF AAT	UNITS:	mm
DWG NO.		CHECKED:		TOLERANCE	± 0.5
		APPROVAL:		FIRST ANGLE PROJECTION	
		MATERIAL:	LCP		



ADVANCED ACOUSTIC TECHNOLOGY CORPORATION

For more information, please contact AATC.

AATC

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

AATC:

ADI-1005S-C-1