

1. SPECIFICATIONS

AMF-O60C40-NA-LF


01	Electret's Type	Foil type
02	Sensitivity	-40±3dB (0dB=1V/Pa,1KHz)
03	Standard Operation Voltage	2.0 V
04	Output Impedance	2.2 KΩ
05	Directivity	Omni directional
06	Frequency Range	100- 10K Hz
07	Max. Operation Voltage	10V
08	Current Consumption	Max.0.5mA
09	Sensitivity Reduction	Within -3dB 0dB=1V/Pa,1KHz Vs=2.0to 1.5V
10	S/N Ratio	≥ 58dB
11	Sound Pressure Level	110 dB
12	Operating Temperature	-20~+60℃
13	Storage Temperature	-25~+70℃

REV NO.

REVISION NOTE

APPROVAL

DATE



TITLE: MICROPHONE

DRAWN: *Jack* 2016/06/27

SCALE: 5:1 SHEET: 1 of 1

PART NO. AMF-060C40-NA-LF

DESIGNED: R & D OF AAT

UNITS: mm

DWG NO.

3

CHECKED:

TOLERANCE ± 0.2

APPROVAL:

UNLESS OTHERWISE SPECIFIED:

ONE PLACE DECIMAL $\pm$ ***TWO PLACE DECIMAL $\pm$ ***THREE PLACE DECIMAL $\pm$ ***

F6050AL-SB-403 11559

REV

MATERIAL: AL



ADVANCED ACOUSTIC TECHNOLOGY CORPORATION

For more information, please contact AATC.

AATC

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[AATC:](#)

[AMF-O60C40-NA-LF](#)