


NYLON-INSULATED (FLARED) BUTT SPLICE CONNECTORS



MAXIMUM ELECTRIC CURRENT:

A.W.G.	22	20	18	16	14	12	10
AMP.	9	12	17	18	30	35	50

MAXIMUM ELECTRICAL RATING: 105°C 600 VOLTS MAX.

CONNECTOR MATERIAL: COPPER INSULATION MATERIAL: NYLON

INSULATION COLOR:

22-16 A.W.G.: RED ■ 16-14 A.W.G.: BLUE ■ 12-10 A.W.G.: YELLOW ■

WIRE RANGE A.W.G. mm ²	ITEM NO.	DIMENSION ^{inch} mm			MATERIAL	CRIMPING TOOL	Q'TY BOX
		L	D	d1			
22-16 A.W.G. 0.5-1.5 mm ²	BNYTF1	.992 25.2	.157 4.0	.067 1.7	COPPER TUBULAR	K.S. MODEL KST2000A HRI-126J WITH DIE INDEX COLOR:RED	1000
16-14 A.W.G. 1.5-2.5 mm ²	BNYTF2	.992 25.2	.177 4.5	.091 2.3	COPPER TUBULAR	K.S. MODEL KST2000A HRI-126J WITH DIE INDEX COLOR:BLUE	1000
12-10 A.W.G. 4-6 mm ²	BNYTF5	1.110 28.2	.248 6.3	.134 3.4	COPPER TUBULAR	K.S. MODEL KST2000A HRI-126J WITH DIE INDEX COLOR:YELLOW	500
22-16 A.W.G. 0.5-1.5 mm ²	BNYF1	.992 25.2	.157 4.0	.067 1.7	COPPER PLATE	K.S. MODEL KST2000A HRI-126J WITH DIE INDEX COLOR:RED	1000
16-14 A.W.G. 1.5-2.5 mm ²	BNYF2	.992 25.2	.177 4.5	.091 2.3	COPPER PLATE	K.S. MODEL KST2000A HRI-126J WITH DIE INDEX COLOR:BLUE	1000
12-10 A.W.G. 4-6 mm ²	BNYF5	1.110 28.2	.248 6.3	.130 3.3	COPPER PLATE	K.S. MODEL KST2000A HRI-126J WITH DIE INDEX COLOR:YELLOW	500

  ALL LISTED

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[KS Terminals:](#)

[BNYF1](#) [BNYF2](#) [BNYF5](#)