


NON-INSULATED BLADE TERMINALS


MAXIMUM ELECTRIC CURRENT:

A.W.G.	26	24	22	20	18	16	14
AMP.	5.5	7	9	12	17	18	30

TERMINAL MATERIAL: COPPER

WIRE RANGE A.W.G. mm ²	ITEM NO.		DIMENSION ^{inch} mm							CRIMPING TOOL	Q'TY BOX	
	BRAZED SEAM	BUTTED SEAM	W	F	L	E	D	d1	T			
26-22 A.W.G. 0.2-0.5 mm ²	DBNB0.5-8	DBN0.5-8	.059 1.5	.315 8.0	.472 12.0	.157 4.0	.087 2.2	.039 1.0	.020 0.5	IZUMI MODEL KSTHT-203 WITH DIE INDEX NO:(INSUL)16-22	1000	
22-16 A.W.G. 0.5-1.5 mm ²	DBNB1-9	DBN1-9	.110 2.8	.354 9.0	.543 13.8	.189 4.8	.134 3.4	.067 1.7	.030 0.75	IZUMI MODEL 5N18 WITH DIE INDEX NO:1.25	1000	
	DBNB1-10	DBN1-10	.091 2.3	.394 10.0	.583 14.8					1000		
	DBNB1-11	DBN1-11	.118 3.0	.433 11.0	.622 15.8					OR	1000	
	DBNBS1-13 [*]	DBNS1-13 [*]	.075 1.9	.512 13.0	.701 17.8					K.S. MODEL KST2000D-1322 WITH DIE INDEX NO:22-18	1000	
	DBNB1-13	DBN1-13	.118 3.0							1000		
	DBNB1-14	DBN1-14	.118 3.0	.551 14.0	.740 18.8					OR	K.S. MODEL KM-70L WITH DIE SET NO. DIE-1322 WITH DIE INDEX NO:22-18	1000
	DBNB1-18	DBN1-18	.087 2.2	.709 18.0	.898 22.8					1000		
	DBNBS1-18	DBNS1-18	.079 2.0							1000		
16-14 A.W.G. 1.5-2.5 mm ²	DBNB2-9	DBN2-9	.110 2.8	.354 9.0	.543 13.8	.189 4.8	.161 4.1	.091 2.3	.031 0.8	IZUMI MODEL 5N18 WITH DIE INDEX NO:2 OR K.S. MODEL KST2000D-1322 WITH DIE INDEX NO:16-14 OR K.S. MODEL KM-70L WITH DIE SET NO. DIE-1322 WITH DIE INDEX NO.16-14	1000	
	DBNB2-10	DBN2-10	.094 2.4	.394 10.0	.583 14.8						1000	
	DBNB2-13	DBN2-13	.094 2.4	.512 13.0	.701 17.8						1000	
	DBNBL2-13	DBNL2-13	.118 3.0								1000	
	DBNBLL2-13	DBNLL2-13	.177 4.5	.551 14.0	.740 18.8						1000	
	DBNBS2-14 [⊙]	DBNS2-14 [⊙]	.083 2.1								1000	
	DBNB2-14	DBN2-14	.094 2.4								1000	
	DBNBL2-14	DBNL2-14	.118 3.0	.709 18.0	.898 22.8						1000	
	DBNBS2-18	DBNS2-18	.079 2.0								1000	
	DBNB2-18	DBN2-18	.087 2.2								1000	
	DBNBL2-18	DBNL2-18	.110 2.8								1000	



ALL LISTED

◎ : NOT UL AND C-UL LISTED

※ : DEVELOPING ON DEMAND

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

KS Terminals:

[DBNB1-10](#) [DBNB1-11](#) [DBNB1-13](#) [DBNB1-14](#) [DBNB1-18](#) [DBNB1-9](#) [DBNB2-10](#) [DBNB2-13](#) [DBNB2-14](#) [DBNB2-18](#)
[DBNB2-9](#) [DBNBL2-13](#) [DBNBL2-14](#) [DBNBL2-18](#) [DBNBLL2-13](#) [DBNBS1-18](#) [DBNBS2-18](#)