


NYLON-INSULATED BLADE TERMINALS

MAXIMUM ELECTRIC CURRENT:

A.W.G.	26	24	22	18	16	14
AMP.	5.5	7	9	17	18	30

MAXIMUM ELECTRICAL RATING: 105°C 600 VOLTS MAX.
INSULATION MATERIAL: NYLON
INSULATION COLOR:

26-22 A.W.G.: YELLOW 22-16 A.W.G.: RED 16-14 A.W.G.: BLUE

TERMINAL MATERIAL: COPPER


WIRE RANGE A.W.G. mm ²	ITEM NO.		DIMENSION inch mm							CRIMPING TOOL	Q'TY BOX
	BRAZED SEAM	BUTTED SEAM	W	F	L	E	D	d1	T		
26-22 A.W.G. 0.2-0.5 mm ²	DBNYB0.5-8	DBNY0.5-8	.059 1.5	.315 8.0	.630 16.0	.315 8.0	.087 2.2	.039 1.0	.020 0.5	K.S. MODEL LY8-067 WITH DIE INDEX NO:0.5	1000
22-16 A.W.G. 0.5-1.5 mm ²	DBNYB1-9	DBNY1-9	.110 2.8	.354 9.0	.780 19.8	.433 11.0	.157 4.0	.067 1.7	.030 0.75	IZUMI MODEL 34 WITH DIE INDEX COLOR:RED OR K.S. MODEL KST2000A HRI-126J WITH DIE INDEX COLOR:RED	1000
	DBNYB1-10	DBNY1-10	.091 2.3	.394 10.0	.819 20.8						1000
	DBNYB1-11	DBNY1-11	.118 3.0	.433 11.0	.858 21.8						1000
	DBNYBS1-13	DBNYS1-13	.075 1.9	.512 13.0	.937 23.8						1000
	DBNYB1-13	DBNY1-13	.118 3.0								1000
	DBNYB1-14	DBNY1-14	.118 3.0	.551 14.0	.976 24.8						1000
	DBNYB1-18	DBNY1-18	.087 2.2	.709 18.0	1.134 28.8						1000
	DBNYBS1-18	DBNYS1-18	.079 2.0								1000
16-14 A.W.G. 1.5-2.5 mm ²	DBNYB2-9	DBNY2-9	.110 2.8	.354 9.0	.780 19.8	.433 11.0	.177 4.5	.091 2.3	.031 0.8	IZUMI MODEL 34 WITH DIE INDEX COLOR:BLUE OR K.S. MODEL KST2000A HRI-126J WITH DIE INDEX COLOR:BLUE	1000
	DBNYB2-10	DBNY2-10	.094 2.4	.394 10.0	.819 20.8						1000
	DBNYB2-13	DBNY2-13	.094 2.4	.512 13.0	.937 23.8						1000
	DBNYBL2-13	DBNYL2-13	.118 3.0								1000
	DBNYBLL2-13	DBNYLL2-13	.177 4.5	.512 13.0	.945 24.0						1000
	DBNYBS2-14	DBNYS2-14	.083 2.1	.551 14.0	.976 24.8						1000
	DBNYB2-14	DBNY2-14	.094 2.4								1000
	DBNYBL2-14	DBNYL2-14	.118 3.0								1000
	DBNYBS2-18	DBNYS2-18	.079 2.0	.709 18.0	1.134 28.8						1000
	DBNYB2-18	DBNY2-18	.087 2.2								1000
	DBNYBL2-18	DBNYL2-18	.110 2.8								1000



ALL LISTED

◎: NOT UL AND C-UL LISTED

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

KS Terminals:

[DBNY1-11](#) [DBNY1-14](#) [DBNY1-9](#) [DBNY2-13](#) [DBNY2-18](#) [DBNYL2-13](#)