


DIN 46237

NYLON-INSULATED RING TERMINALS

MAXIMUM ELECTRIC CURRENT:

A.W.G.	26	24	22	20	18	16	14
AMP.	5.5	7	9	12	17	18	30

MAXIMUM ELECTRICAL RATING: 105°C 600 VOLTS MAX.
INSULATION MATERIAL: NYLON
INSULATION COLOR:

 26-22 A.W.G.: YELLOW 22-16 A.W.G.: RED 16-14 A.W.G.: BLUE
TERMINAL MATERIAL: COPPER


WIRE RANGE A.W.G. mm ²	ITEM NO.		STUD SIZE		DIMENSION mm						CRIMPING TOOL	Q'TY BOX		
	BRAZED SEAM	BUTTED SEAM	d2		d3	l	d1	d4	a	S				
26-22 A.W.G. 0.2-0.5 mm ²	DRNYB2-0.5	DRNY2-0.5	#2	2.2	5.0	14.0	1.0	2.3	8.0	0.5	K.S. MODEL LY8-067 WITH DIE INDEX NO:0.5	1000		
	DRNYB2.5-0.5	DRNY2.5-0.5	#3	2.7								1000		
	DRNYB3-0.5	DRNY3-0.5	#4	3.2								1000		
	DRNYB3.5-0.5	DRNY3.5-0.5	#6	3.7	6.0	16.0						1000		
	DRNYB4-0.5	DRNY4-0.5	#8	4.3								1000		
	DRNYB5-0.5	DRNY5-0.5	#10	5.3								8.0	1000	
22-16 A.W.G. 0.5-1.5 mm ²	DRNYB2-1	DRNY2-1	#2	2.2	6.0	17.0	1.6	4.0	11.0	0.8	IZUMI MODEL 34 WITH DIE INDEX COLOR:RED OR K.S. MODEL KST2000A HRI-126J WITH DIE INDEX COLOR:RED	1000		
	DRNYB2.5-1	DRNY2.5-1	#3	2.7								1000		
	DRNYB3-1	DRNY3-1	#4	3.2								1000		
	DRNYB3.5-1	DRNY3.5-1	#6	3.7								1000		
	DRNYBS4-1	DRNYS4-1	#8	4.3	7.0	17.5						8.0	18.0	1000
	DRNYB4-1	DRNY4-1	#8	4.3	18.5	1000								
	DRNYBS5-1	DRNYS5-1	#10	5.3	10.0	19.0						1000		
	DRNYB5-1	DRNY5-1	#10	5.3								1000		
	DRNYB6-1	DRNY6-1	1/4	6.5								11.0	21.0	1000
	DRNYBL6-1	DRNYL6-1	1/4	6.5										1000
	DRNYB8-1	DRNY8-1	5/16	8.4	14.0	23.0						1000		
	DRNYB10-1	DRNY10-1	3/8	10.5								1000		
	DRNYBL10-1	DRNYL10-1	3/8	10.5								18.0	25.0	1000
	16-14 A.W.G. 1.5-2.5 mm ²	DRNYB3-2.5	DRNY3-2.5	#4	3.2	6.0						17.0	2.3	4.5
DRNYB3.5-2.5		DRNY3.5-2.5	#6	3.7	1000									
DRNYBS4-2.5		DRNYS4-2.5	#8	4.3	6.8	17.6	1000							

UL cUL ALL LISTED

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

KS Terminals:

[DRNY2.5-0.5](#) [DRNY2.5-1](#) [DRNY2-0.5](#) [DRNY3.5-0.5](#) [DRNY3-0.5](#) [DRNY3-2.5](#) [DRNY4-0.5](#) [DRNY5-0.5](#)