


DIN 46237

NYLON-INSULATED RING TERMINALS



MAXIMUM ELECTRIC CURRENT:

A.W.G.	2/0	3/0	4/0	250	300
AMP.	265	310	360	405	445

MAXIMUM ELECTRICAL RATING: 105°C 600 VOLTS MAX.

INSULATION MATERIAL: NYLON **TERMINAL MATERIAL: COPPER**

INSULATION COLOR:

2/0 A.W.G.: YELLOW 3/0 A.W.G.: RED 4/0 A.W.G.: BLUE

250/300 MCM A.W.G.: YELLOW

WIRE RANGE A.W.G. mm ²	ITEM NO.		STUD SIZE		DIMENSION mm						CRIMPING TOOL	Q'TY BOX
	BRAZED SEAM	BUTTED SEAM	d2		d3	l	d1	d4	a	S		
2/0 A.W.G. 70 mm ²	DRNYB6-70		1/4	6.5	22.0	51.0	13.0	18.7	31.5	2.0	KLAUKE MODEL PK25/2 WITH DIE INDEX NO: HIS 25/70	50
	DRNYB8-70		5/16	8.4								50
	DRNYB10-70		3/8	10.5								50
	DRNYB12-70		1/2	13.0								50
	DRNYB16-70		5/8	17.0	28.0	55.0						50
3/0 A.W.G. 95 mm ²	DRNYB8-95		5/16	8.4	24.0	57.5	15.0	21.7	35.5	2.5	KLAUKE MODEL PK25/2 WITH DIE INDEX NO: HIS 25/95	50
	DRNYB10-95		3/8	10.5								50
	DRNYB12-95		1/2	13.0								25
	DRNYB16-95		5/8	17.0	28.0	59.5						25
4/0 A.W.G. 120 mm ²	DRNYB8-120		5/16	8.4	24.0	62.0	16.5	24.2	40.0	3.0	KLAUKE MODEL PK25/2 WITH DIE INDEX NO: HIS 25/120	50
	DRNYB10-120		3/8	10.5								25
	DRNYB12-120		1/2	13.0								25
	DRNYB16-120		5/8	17.0	28.0	66.0						25
250/300 MCM 150 mm ²	DRNYB10-150		3/8	10.5	30.0	70.0	19.0	27.2	44.0	3.2	KLAUKE MODEL PK25/2 WITH DIE INDEX NO: HIS 25/150	25
	DRNYB12-150		1/2	13.0								25
	DRNYB16-150		5/8	17.0								25

UL cUL ALL LISTED

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

KS Terminals:

[DRNYB10-150](#) [DRNYB10-70](#) [DRNYB10-95](#) [DRNYB12-150](#) [DRNYB12-70](#) [DRNYB8-70](#)