


DIN 46234

NON-INSULATED SPADE TERMINALS

MAXIMUM ELECTRIC CURRENT:

A.W.G.	26	24	22	20	18	16	14	12	10
AMP.	5.5	7	9	12	17	18	30	35	50

TERMINAL MATERIAL: COPPER



WIRE RANGE A.W.G. mm ²	ITEM NO.	STUD SIZE		DIMENSION mm						CRIMPING TOOL	Q'TY BOX
		d2		d3	l	a	C	d1	S		
26-22 A.W.G. 0.2-0.5 mm ²	DSNB2-0.5	#2	2.2	5.0	8.0	4.0	2.0	1.0	0.5	K.S. MODEL KSTHT-203 WITH DIE INDEX NO:(INSUL)16-22	1000
	DSNB3-0.5	#4	3.2								1000
	DSNB3.5-0.5	#6	3.7	6.0	11.0						1000
	DSNB4-0.5	#8	4.3	6.5							1000
	DSNB5-0.5	#10	5.3	8.0							1000
22-16 A.W.G. 0.5-1.5 mm ²	DSNB3-1	#4	3.2	6.0	11.0	5.0	4.0	1.6	0.8	IZUMI MODEL 5N18 WITH DIE INDEX NO:1.25 OR K.S. MODEL KST2000D-1322 LY-2045A WITH DIE INDEX NO:1.25	1000
	DSNB3.5-1	#6	3.7								1000
	DSNB4-1	#8	4.3	6.8	12.0						1000
	DSNBL4-1	#8	4.3	8.0							1000
	DSNB5-1	#10	5.3	10.0	13.0						1000
	DSNB6-1	1/4	6.5	11.0	15.0						1000
16-14 A.W.G. 1.5-2.5 mm ²	DSNB3-2.5	#4	3.2	5.5	13.0	5.0	4.5	2.3	0.8	IZUMI MODEL 5N18 WITH DIE INDEX NO:2 OR K.S. MODEL KST2000D-1322 LY-2045A WITH DIE INDEX NO:2	1000
	DSNB3.5-2.5	#6	3.7	6.0	11.0						1000
	DSNB4-2.5	#8	4.3	6.8	12.0						1000
	DSNBL4-2.5	#8	4.3	8.0							1000
	DSNB5-2.5	#10	5.3	10.0	14.0						1000
	DSNB6-2.5	1/4	6.5	11.0	16.0						1000
12-10 A.W.G. 2.5-6 mm ²	DSNB4-6	#8	4.3	8.0	14.0	6.0	6.0	3.6	1.0	IZUMI MODEL 5N18 WITH DIE INDEX NO:5.5 OR K.S. MODEL KST2000D-1322 LY-2045A WITH DIE INDEX NO:5.5	1000
	DSNB5-6	#10	5.3	10.0	15.0						1000
	DSNB6-6	1/4	6.5	11.0	16.0						1000
	DSNB8-6	5/16	8.4	14.0	19.0						1000
	DSNB10-6	3/8	10.5	18.0	21.0						500

UL cUL ALL LISTED

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

KS Terminals:

[DSNB10-6](#) [DSNB2-0.5](#) [DSNB3.5-0.5](#) [DSNB3.5-1](#) [DSNB3-0.5](#) [DSNB3-1](#) [DSNB3-2.5](#) [DSNB4-0.5](#) [DSNB4-1](#)
[DSNB4-2.5](#) [DSNB4-6](#) [DSNB5-0.5](#) [DSNB5-1](#) [DSNB5-2.5](#) [DSNB5-6](#) [DSNB6-1](#) [DSNB6-2.5](#) [DSNB6-6](#) [DSNB8-6](#)
[DSNBL4-1](#) [DSNBL4-2.5](#)