

NYLON-FULLY INSULATED FEMALE DISCONNECTORS (A TYPE)

MAXIMUM ELECTRIC CURRENT:

A.W.G.	26	24	22	20	18	16	14
AMP.	2	2	3	4	7	10	15

MAXIMUM ELECTRICAL RATING: 105°C 600 VOLTS MAX.


INSULATION MATERIAL: NYLON TERMINAL MATERIAL: BRASS

INSULATION COLOR:

26-22 A.W.G.: VIOLET 22-18 A.W.G.: RED 16-14 A.W.G.: BLUE

TERMINAL BARREL I.D.:

26-22 A.W.G.: C=0.8mm 22-18 A.W.G.: C=1.6mm 16-14 A.W.G.: C=2.3mm



WIRE RANGE A.W.G. mm ²	ITEM NO.	NEMA TAB	DIMENSION inch mm						CRIMPING TOOL	Q'TY BOX
			W	F	L	B	D	T		
26-22 A.W.G. 0.2-0.5 mm ²	FDFNY0.5-110(5)A [Ⓢ]	.020x.110 (0.5x2.8)	.126 3.2	.256 6.5	.709 18.0	.346 8.8	.102 2.6	.012 0.3		1000
	FDFNY0.5-110(8)A [Ⓢ]	.032x.110 (0.8x2.8)		.265 6.5						1000
	FDFNY0.5-187(5)A [Ⓢ]	.020x.187 (0.5x4.75)	.197 5.0	.252 6.4	.811 20.6	.346 8.8	.102 2.6	.012 0.3		1000
	FDFNY0.5-187(8)A [Ⓢ]	.032x.187 (0.8x4.75)								1000
22-18 A.W.G. 0.5-0.75 mm ²	FDFNY1-110(5)A [Ⓢ]	.020x.110 (0.5x2.8)	.126 3.2	.252 6.4	.709 18.0	.346 8.8	.126 3.2	.012 0.3		1000
	FDFNY1-110(8)A [Ⓢ]	.032x.110 (0.8x2.8)								1000
	FDFNY1-187(5)A	.020x.187 (0.5x4.75)	.197 5.0	.252 6.4	.827 21.0	.394 10.0	.146 3.7	.014 0.35	K.S. MODEL KST3000CA1 WITH DIE INDEX COLOR:RED	1000
	FDFNY1-187(8)A	.032x.187 (0.8x4.75)							1000	
	FDFNY1-250A	.032x.250 (0.8x6.35)	.260 6.6	.299 7.6	.827 21.0	.394 10.0	.146 3.7	.016 0.4	K.S. MODEL KST3000CA2 WITH DIE INDEX COLOR:RED	1000
16-14 A.W.G. 1.5-2.5 mm ²	FDFNY2-110(5)A [Ⓢ]	.020x.110 (0.5x2.8)	.126 3.2	.252 6.4	.748 19.0	.386 9.8	.173 4.4	.012 0.3		1000
	FDFNY2-110(8)A [Ⓢ]	.032x.110 (0.8x2.8)								1000
	FDFNY2-187(5)A	.020x.187 (0.5x4.75)	.197 5.0	.252 6.4	.827 21.0	.394 10.0	.173 4.4	.014 0.35	K.S. MODEL KST3000CA1 WITH DIE INDEX COLOR:BLUE	1000
	FDFNY2-187(8)A	.032x.187 (0.8x4.75)							1000	
	FDFNY2-250A	.032x.250 (0.8x6.35)	.260 6.6	.299 7.6	.827 21.0	.394 10.0	.173 4.4	.016 0.4	K.S. MODEL KST3000CA2 WITH DIE INDEX COLOR:BLUE	1000



ALL LISTED

Ⓢ: NOT UL AND C-UL LISTED

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

KS Terminals:

[FDFNY0.5-110\(5\)A](#) [FDFNY0.5-110\(8\)A](#) [FDFNY1-110\(5\)A](#) [FDFNY1-110\(8\)A](#) [FDFNY1-187\(5\)A](#) [FDFNY1-187\(8\)A](#)
[FDFNY1-250A](#) [FDFNY2-110\(5\)A](#) [FDFNY2-110\(8\)A](#) [FDFNY2-187\(5\)A](#) [FDFNY2-187\(8\)A](#) [FDFNY2-250A](#)