


NON-INSULATED FLAG TERMINALS


MAXIMUM ELECTRIC CURRENT:

A.W.G.	22	20	18	16	14	12	10	8	6	4	2
AMP.	9	12	17	18	30	35	50	70	95	125	170

TERMINAL MATERIAL: COPPER

WIRE RANGE A.W.G. mm ²	ITEM NO.	STUD SIZE		DIMENSION inch mm						CRIMPING TOOL	Q'TY BOX						
	BRAZED SEAM	d2		W	F	D	L	d1	T								
22-16 A.W.G. 0.5-1.5 mm ²	FGNB1-5	#10	.209 5.3	.378 9.6	.315 8.0	.134 3.4	.642 16.3	.067 1.7	.030 0.75	IZUMI MODEL KST2000D-FG WITH DIE INDEX NO.:16-14	1000						
16-14 A.W.G. 1.5-2.5 mm ²	FGNB2-3	#4	.126 3.2							IZUMI MODEL KST2000D-FG WITH DIE INDEX NO.:16-14	1000						
	FGNB2-5	#10	.209 5.3									.378 9.6	.287 7.3	.161 4.1	.642 16.3	.091 2.3	.031 0.8
	FGNB2-6	1/4	.252 6.4														
12-10 A.W.G. 4-6 mm ²	FGNB5-4	#8	.169 4.3							ABKIO MODEL 0695U WITH DIE INDEX NO:1	1000						
	FGNB5-5	#10	.209 5.3									.378 9.6	.291 7.4	.220 5.6	.701 17.8	.134 3.4	.039 1.0
	FGNB5-6	1/4	.252 6.4														
8 A.W.G. 8 mm ²	FGNB8-5	#10	.209 5.3	.500 12.7	.358 9.1		.906 23.0			K.S. MODEL KH-150 WITH DIE INDEX NO:10 OR ABKIO MODEL 0695U WITH DIE INDEX NO:2	500						
	FGNB8-6	1/4	.252 6.4														
	FGNBL8-6	1/4	.252 6.4				.283 7.2						.177 4.5	.047 1.2			
	FGNB8-8	5/16	.331 8.4			.610 15.5		.516 13.1	1.114 28.3								
	FGNB8-10	3/8	.413 10.5														
6 A.W.G. 14 mm ²	FGNB14-6	1/4	.252 6.4	.500 12.7	.378 9.6	.354 9.0	.980 24.9	.228 5.8		K.S. MODEL KH-150 WITH DIE INDEX NO:16 OR ABKIO MODEL 0695U WITH DIE INDEX NO:3	500						
	FGNB14-8	5/16	.331 8.4									.630 16.0	.531 13.5	1.201 30.5			
4 A.W.G. 22 mm ²	FGNB22-6	1/4	.252 6.4	.551 14.0	.382 9.7		1.110 28.2			K.S. MODEL KH-150 WITH DIE INDEX NO:25 OR ABKIO MODEL 0695U WITH DIE INDEX NO:4	250						
	FGNB22-8	5/16	.331 8.4									.689 17.5	.543 13.8	.453 11.5	1.339 34.0	.303 7.7	.067 1.7
	FGNB22-10	3/8	.413 10.5														
2 A.W.G. 38 mm ²	FGNB38-6	1/4	.252 6.4							K.S. MODEL KH-150 WITH DIE INDEX NO:35 OR ABKIO MODEL 0695U WITH DIE INDEX NO:5	200						
	FGNB38-8	5/16	.331 8.4									.720 18.3	.535 13.6	.524 13.3	1.421 36.1	.370 9.4	.071 1.8
	FGNB38-10	3/8	.413 10.5														

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

KS Terminals:

[FGNB100-10](#) [FGNB100-8](#) [FGNB14-6](#) [FGNB14-8](#) [FGNB1-5](#) [FGNB22-6](#) [FGNB22-8](#) [FGNB2-5](#) [FGNB2-6](#) [FGNB38-10](#) [FGNB38-6](#) [FGNB38-8](#) [FGNB5-4](#) [FGNB5-5](#) [FGNB5-6](#) [FGNB60-10](#) [FGNB60-6](#) [FGNB60-8](#) [FGNB70-10](#) [FGNB70-8](#) [FGNB80-10](#) [FGNB8-10](#) [FGNB8-5](#) [FGNB8-6](#) [FGNB8-8](#)