

HEAT SHRINKABLE-RING TERMINALS "HB"(BRAZED TYPE)

MAXIMUM ELECTRIC CURRENT:


A.W.G.	8
AMP.	70

MAXIMUM ELECTRICAL RATING: 600 VOLTS MAX.

SHRINK TEMP.: 150°C OPERATING TEMP.: -40°C~+105°C

INSULATION MATERIAL: HIGH DENSITY PE.

TERMINAL MATERIAL: COPPER



WIRE RANGE A.W.G. mm ²	ITEM NO.	DIMENSION						INSULATED COLOR	CRIMPING TOOL	Q'TY BOX
		d2		W		L				
		inch	mm	inch	mm	inch	mm			
8 A.W.G. 8 mm ²	RHB8-3.7	#6	3.7	.315	8.0	1.366	34.7	RED	K.S. MODEL LY-20450 OR IZUMI MODEL 8 WITH DIE INDEX NO:8	500
	RHBS8-4	#8	4.3							500
	RHBL8-4	#8	4.3	.472	12.0	1.457	37.0			500
	RHBS8-5	#10	5.3	.346	8.8					500
	RHBM8-5	#10	5.3	.472	12.0					500
	RHBL8-5	#10	5.3	.591	15.0	1.693	43.0			500
	RHBS8-6	1/4	6.4	.472	12.0	1.457	37.0			500
	RHBL8-6	1/4	6.4	.591	15.0	1.693	43.0			500
	RHB8-8	5/16	8.4							500
	RHB8-10	3/8	10.5							500
	RHB8-12	1/2	13.0	.787	20.0	1.839	46.7			500
	RHB8-14	9/16	15.0	1.244	31.6	2.469	62.7			500
	RHB8-16	5/8	17.0							500
	RHB8-18	11/16	19.0							500
	RHB8-20	3/4	21.0							500

cUL_{us} ALL LISTED

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[KS Terminals:](#)

[RHB8-10](#) [RHB8-8](#) [RHBM8-5](#) [RHBS8-6](#)