


NON-INSULATED RING TERMINALS


MAXIMUM ELECTRIC CURRENT:

A.W.G.	14	12	10
AMP.	30	35	50

TERMINAL MATERIAL: COPPER
SURFACE TREATMENT: TIN PLATED

WIRE RANGE A.W.G. mm ²	ITEM NO.		STUD SIZE		DIMENSION ^{inch} mm							CRIMPING TOOL	Q'TY BOX
	BRAZED SEAM	BUTTED SEAM	d2		W	F	L	E	D	d1	T		
14-12 A.W.G. 2.5-4 mm ²	RNBS3-3.2	RNS3-3.2	#4	.126 3.2	.217 5.5		.661 16.8	.236 6.0	.201 5.1	.114 2.9	.039 1.0	IZUMI MODEL 5N18 WITH DIE INDEX NO.:5.5 OR K.S. MODEL KST2000D-1322 WITH DIE INDEX NO.:12-10 OR K.S. MODEL KM-70L WITH DIE SET NO:DIE-1322 WITH DIE INDEX NO.:12-10	1000
	RNB3-3.2	RN3-3.2	#4	.126 3.2	.315 8.0		.709 18.0						1000
	RNBS3-4	RNS3-4	#8	.169 4.3	.283 7.2	.315 8.0	.693 17.6						1000
	RNB3-4	RN3-4	#8	.169 4.3	.315 8.0		.709 18.0						1000
	RNBS3-5	RNS3-5	#10	.209 5.3									1000
	RNBM3-5	RNM3-5	#10	.209 5.3	.374 9.5	.362 9.2	.787 20.0						1000
	RNBL3-5	RNL3-5	#10	.209 5.3	.472 12.0	.370 9.4	.843 21.4						1000
	RNB3-6	RN3-6	1/4	.252 6.4									1000
	RNB3-8	RN3-8	5/16	.331 8.4	.591 15.0	.524 13.3	1.063 27.0						1000
	RNB3-10	RN3-10	3/8	.413 10.5									1000
	RNB3-12	RN3-12	1/2	.512 13.0	.756 19.2	.630 16.0	1.244 31.6						1000
	12-10 A.W.G. 4-6 mm ²	RNB5-3.2	RN5-3.2	#4	.126 3.2	.283 7.2	.228 5.8						.610 15.5
RNB5-3.7		RN5-3.7	#6	.146 3.7	.240 6.1		.618 15.7	1000					
RNBL5-3.7		RNL5-3.7	#6	.146 3.7	.374 9.5	.327 8.3	.748 19.0	1000					
RNBS5-4		RNS5-4	#8	.169 4.3	.283 7.2	.240 6.1	.618 15.7	1000					
RNBL5-4		RNL5-4	#8	.169 4.3	.374 9.5	.327 8.3	.748 19.0	1000					
RNB5-5		RN5-5	#10	.209 5.3	.374 9.5	.327 8.3	.748 19.0	1000					
RNBL5-5		RNL5-5	#10	.209 5.3	.488 12.4	.496 12.6	.976 24.8	1000					
RNB5-6		RN5-6	1/4	.252 6.4	.472 12.0	.413 10.5	.886 22.5	1000					
RNBM5-6		RNM5-6	1/4	.252 6.4		.512 13.0	.984 25.0	1000					
RNB5-7		RN5-7	5/16	.291 7.4	.413 10.5	.878 22.3	1000						
RNBS5-8		RNS5-8	5/16	.331 8.4		.591 15.0	.441 11.2	.972 24.7	1000				



ALL LISTED

* : ADDITIONAL CERTIFIED

※ : DEVELOPING ON DEMAND

■ : 90D available

Products can be bend to 90-degrees angle.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

KS Terminals:

[RNB3-10](#) [RNB3-12](#) [RNB3-3.2](#) [RNB3-4](#) [RNB3-6](#) [RNB3-8](#) [RNB5-3.2](#) [RNB5-3.7](#) [RNBL3-5](#) [RNBL5-3.7](#) [RNBL5-5](#)
[RNBM3-5](#) [RNBM5-6](#) [RNBS3-3.2](#) [RNBS3-4](#) [RNBS3-5](#) [RNBS5-4](#) [RNB5-5](#) [RNB5-6](#) [RNBL5-4](#)