


NON-INSULATED RING TERMINALS

MAXIMUM ELECTRIC CURRENT:

A.W.G.	8	6
AMP.	70	95

TERMINAL MATERIAL: COPPER
SURFACE TREATMENT: TIN PLATED


WIRE RANGE A.W.G. mm ²	ITEM NO.		STUD SIZE		DIMENSION inch mm							CRIMPING TOOL	Q'TY BOX
	BRAZED SEAM	BUTTED SEAM	d2		W	F	L	E	D	d1	T		
8 A.W.G. 8 mm ²	RNB8-14		9/16	.591 15.0									500
	RNB8-16		5/8	.669 17.0									500
	RNB8-18		11/16	.748 19.0	1.244 31.6	1.008 25.6	1.949 49.5	.335 8.5	.283 7.2	.177 4.5	.047 1.2		500
	RNB8-20		3/4	.827 21.0									500
	RNB8-22		7/8	.906 23.0									500
6 A.W.G. 14 mm ²	RNB14-4 ■		#8	.169 4.3	.472 12.0		1.150 29.2						500
	RNBS14-5 ■		#10	.209 5.3	.374 9.5		1.110 28.2						500
	RNB14-5 ■		#10	.209 5.3	.472 12.0	.524 13.3	1.150 29.2						500
	RNBSS14-6		1/4	.252 6.4	.374 9.5		1.110 28.2						500
	RNBS14-6 ■*		1/4	.252 6.4	.472 12.0		1.150 29.2						500
	RNBL14-6		1/4	.252 6.4									500
	RNB14-8 ■*		5/16	.331 8.4	.630 16.0	.559 14.2	1.280 32.5	.413 10.5	.354 9.0	.228 5.8	.059 1.5		500
	RNB14-10 ■*		3/8	.431 10.5									500
	RNB14-11		7/16	.453 11.5	.866 22.0	.780 19.8	1.614 41.0						250
	RNB14-12		1/2	.512 13.0									250
	RNB14-14		9/16	.591 15.0									250
	RNB14-16		5/8	.669 17.0	1.244 31.6	.996 25.3	2.008 51.0						250
	RNB14-18		11/16	.748 19.0									250
	RNB14-20		3/4	.827 21.0									250



ALL LISTED

* : ADDITIONAL CERTIFIED

■ : 90D available

Products can be bend to 90-degrees angle.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

KS Terminals:

[RNB14-10](#) [RNB14-11](#) [RNB14-12](#) [RNB14-16](#) [RNB14-20](#) [RNB14-4](#) [RNB14-5](#) [RNB14-8](#) [RNB8-14](#) [RNB8-16](#)
[RNB8-18](#) [RNB8-20](#) [RNB8-22](#) [RNBL14-6](#) [RNBS14-5](#) [RNBS14-6](#) [RNBSS14-6](#)