



VOC-Free Flux Remover UltraClean™

- VOC-exempt formula
- Highly effective on no-clean fluxes
- Removes rosin-based fluxes, pastes, and silicone residues on circuit boards
- Medium drying speed
- Strongest non-chlorinated/halogen-free cleaner
- Plastic-safe
- MicroCare TriggerGrip™ cleaning system compatible

Product Information

The MicroCare VOC-Free Flux Remover - *UltraClean* is a non-chlorinated, halogen-free, high-purity cleaning fluid, developed to clean rosin fluxes, “no-clean” fluxes and hard-to-clean lead-free solder pastes. It is the ideal cleaning fluid for perfectly clean printed circuit boards during assembly, manufacturing, rework and repair. It is also suitable for use in cleaning fingerprints, moisture, light oxides, dust and other airborne contamination frequently found on circuit boards that are returned for warranty or service work.

VOC-Free Flux Remover - *UltraClean* is the strongest halogen-free flux remover on the market. It has low odor, medium cleaning strength and dries moderately fast. It is non-corrosive and dries with no residue; and no rinsing required.

All ingredients of the VOC-Free Flux Remover - *UltraClean* are designated by the US EPA as VOC-exempt, and this formula complies with California CARB (California Resource Board) and SCAQMD (Southern Coast Air Quality Management District) VOC regulations.

Dispense directly from the can or use with the MicroCare *TriggerGrip* cleaning system for faster, safer and more economical process of cleaning printed circuit boards at the work bench.

AVAILABILITY: Stocked by MicroCare distributors world-wide.

Contact MicroCare for a distributor near you. For more information contact MicroCare directly or visit www.MicroCare.com.

Not all products and packages available in all regions and territories.

Discover Perfectly Clean www.MicroCare.com

MicroCare Corporation




595 John Downey Drive
New Britain, CT 06051 USA
CAGE: OATV9
Tel: +1 860 827 0626
Toll Free: 1 800 638 0125
Email: TechSupport@MicroCare.com

MicroCare Europe Bvba

Vekestraat 29 B11
Industriezone 't Sas
1910 Kampenhout, Belgium
Tel: +32 2 251 95 05
Fax: +32 2 400 96 39
Email: EuroSales@MicroCare.com

MicroCare Asia Pte Ltd

102E Pasir Panjang Road
#03-01 Citilink Warehouse Complex
Singapore 118529
Tel: +65 6271 0182
Email: TechSupport@MicroCare.sg

Technical Details and Cleaning Data	
Boiling Point	85 °C / 187 °F
Chemical Family	Siloxanes & VOC-exempt cleaners
Cleaning Strength (KB value)	56
Evaporation Rate	Medium
Odor	Slight, Ether
Percent Volatile	100%
Specific Gravity	0.85
Health, Safety and Environmental Data	
Flammable	Yes
Flashpoint (TCC)	3 °C / 37.0 °F
Chlorinated	No
Halogen-Free	Yes
NFPA	Health: 1 Fire: 3 Instability: 0
RoHS and WEEE Compliant	Yes
REACH	Yes*
US EPA SNAP-Approved	Yes
GHS / HCS Pictogram	
Packaging	
Aerosol ¹ - 10 oz / 284 g	MCC-VOC10A
Minicube ² - 6 lb / 2.72 kg	MCC-VOCG
Cube ² - 32 lb / 14.5 kg	MCC-VOCP
Drum ¹ - 330 lb / 149 kg	MCC-VOCD
TriggerGrip™ Compatible	Yes (aerosol)
Aerosol Packaging	12 cans / box
Shelf Life	Unlimited
Recycle	 

*Contact MicroCare for specific details

Shown with the reusable MicroCare TriggerGrip cleaning system. This option cuts cleaning costs by reducing fluid use by 66%.



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

MicroCare:

[MCC-VOC10A](#) [MCC-VOCG](#) [MCC-VOCP](#)