


RoHS Compliant

PX-257

PCIe 2xRS232 1MBaud


"SERIAL CARDS ENGINEERED TO EXCEED EXPECTATIONS"



Features

- 2 port RS232
- PCI Express x1, x4, x8 x16 lane slots socket size
- 128 Byte Tx and 128 Byte Rx FIFOs
- Up to 921,600 Baud
- DB9 connector (9 Pin Male)
- Drivers for all popular operating systems
- Sample Programs, Test & Terminal software
- Lifetime Support
- Lifetime Warranty (registration required)

Options



PX-257:
PCIe 2xRS232 1MBaud

Description

PCI Express Card providing two RS232 serial ports. Data transfer rates up to 921,600 baud rates and the 128 byte deep transmit and 128 byte receive FIFOs, delivers uncompromising performance on your PC. Drivers for Windows 32 bit and 64 bit Operating Systems including Windows 2000, XP, Server 2003, Vista, Server 2008, Windows 7 and Windows 8.

PCI Express is the latest standard in PC connectivity.


With Brainboxes' industry renowned Lifetime Warranty and Lifetime Support!

Software

Microsoft signed drivers (easy installation & robust operation) for:

- Windows 7 32 bit 64 bit Editions
- Windows Server 2008 32 bit 64 bit Editions
- Windows Vista 32 bit 64 bit editions
- Windows Server 2003 32 bit 64 bit Editions


As well as: full product documentation, a thorough troubleshooting guide and terminal software. Detailed sample source code for many popular programming languages. Further OS support on next page.



ORDER

Description
PCIe 2xRS232 1MBaud

Code
PX-257



PCIe 2xRS232 1MBaud

PX-257: Full Specification

| | | |
|--------------------------------|--|---|
| Port | Port Connector FIFO size Operating Distance Cable | 2 x RS232 DB9 Connector - 9 Pin Male 128 RX FIFO + 128 TX FIFO EIA - RS232 Standard No Cable; Integrated Connector |
| Port Settings | Port Settings Baud Rate Data Bits Parity Stop Bits Flow Control Tx/Rx Modes | 921,600 5,6,7 or 8 Odd, Even, None, Mark or Space 1, 1.5 or 2 RTS/CTS, DSR/DTR, XON/XOFF Point to Point |
| Interface | Interface OS Compatibility BUS | Microsoft Windows 8 32 bit 64 bit Editions Microsoft Windows 7 32 bit 64 bit Editions Windows Server 2008 32 bit 64 bit Editions Windows Vista 32 bit 64 bit Editions Windows Server 2003 32 bit 64 bit Editions PCI Express x1, x4, x8 x16 lane slots |
| Approvals | Other Approvals Microsoft Approvals | AEO C-TPAT Microsoft Certified Gold Partner WEEE RoHS METL EMC: CE TAA Windows 7 32 bit 64 bit Editions Windows Server 2008 32 bit 64 bit editions Windows Vista 32 bit 64 bit editions Windows Server 2003 32 bit 64 bit editions Windows XP 32 bit 64 bit editions |
| General | PCB Layers Power Consumption Weight Size | 4 380mA @ 3.3V 0.065 kg 130l x 18w x 120h mm |
| Box Content | Packaging Card | Installation CD including manual, Microsoft signed drivers & utilities PCIe 2xRS232 1MBaud No Cable; Integrated Connector |
| Product Support | Warranty Support | Lifetime (online registration required) Lifetime Web, Email and Phone Support from fully qualified, friendly staff who work in and alongside the Product Development Team |
| Additional | OEM option Made In Customisable | Available for bulk buy OEM Manufactured in the UK by Brainboxes Winner 2005 European Electronics Industry Awards "Manufacturer of the Year" Brainboxes operate a "Perfect Fit Custom Design" policy for volume users. More Info: sales@brainboxes.com |

Other PCI Express Cards: 1 Port RS232 | 2 Port RS232 | 4 Port RS232 | 8 Port RS232 | 1 Port RS422/485 | 2 Port RS422/485 | 4 Port RS422/485
 Other Brainboxes Ranges: PCI | Bluetooth Serial Adapter | Ethernet to Serial Adapter | PCMCIA Serial Card | ExpressCard Serial Adapter | USB to Serial

+44(0) 151 220 2500 | sales@brainboxes.com | www.brainboxes.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Brainboxes:

PX-257