


RoHS Compliant

PX-306/PX-272


PCIe 4 + 1xRS232 + 1xLPT Printer Port

"SERIAL CARDS ENGINEERED TO EXCEED EXPECTATIONS"



Features

- 5 x RS232 + 1 x LPT Printer port
- PCI Express x1, x4, x8 x16 lane slots
- Brainboxes' BB16C958 UART
- 128 Byte Tx and 128 Byte Rx FIFOs
- Up to 921,600 Baud
- DB9 Connector 9 Pin Male and LPT port 25 Pin Female
- Drivers for all popular operating systems
- Sample Programs, Test & Terminal software
- Lifetime Support
- Lifetime Warranty (registration required)



Description

PCI Express Card providing five RS232 serial ports and one LPT port 5 industry standard 9 pin D RS232 ports via a quad cable and 1 x 9 Pin D on a fly lead plus a 25 pin D LPT port on a flylead. Brainboxes' own BB16C958 Uart provides datatransfer rates up to 921,600 baud rates and the 128 byte deep transmit and 128 byte receive FIFOs, coupled with 1Mbit/s line drivers deliver uncompromising performance on your PC. Drivers for Windows 32 bit and 64 bit Operating Systems including Windows 2000, XP, Server 2003, Vista, Server 2008, Windows 7 and Linux.

PCI Express is the latest standard in PC connectivity. LPT printers have been used in the industry for years.

With Brainboxes' industry renowned Lifetime Warranty and Lifetime Support!


Software

Microsoft signed drivers (easy installation & robust operation) for:

- Windows 7 32 bit 64 bit Editions
- Windows Server 2008 32 bit 64 bit Editions
- Windows Vista 32 bit 64 bit editions
- SUSE Linux Enterprise Server 10

64 Bit Driver

As well as: full product documentation, a thorough troubleshooting guide and terminal software. Detailed sample source code for many popular programming languages. Further OS support on next page.



Low profile option - PX-272



ORDER

Description

PCIe 4 + 1xRS232 + 1xLPT Printer Port
LP PCIe 4 + 1xRS232 + 1xLPT Printer Port


Code

PX-306



PCIe 4 + 1xRS232 + 1xLPT Printer Port

PX-306/PX-272: Full Specification

Port 	Ports Connector FIFO size Operating Distance Cable Printer Ports Printer Connector	5 x RS232 + 1 x LPT Printer DB9 Connector 9 Pin Male and LPT port 25 Pin Female 128 RX FIFO + 128 TX FIFO EIA - RS232 Standard 4 port cable 44 way D to 4x9 Pin Male D + 1 port 9 Pin Male D on Fly lead 1 25 Pin Female D Connector on Fly Lead
Port Settings 921,600  baud	Baud Rate Data Bits Parity Stop Bits Flow Control Tx/Rx Modes	921,600 5,6,7 or 8 Odd, Even, None 1, 1.5 or 2 RTS/CTS, DSR/DTR, XON/XOFF Point to Point
Interface 	OS Compatibility BUS	Microsoft Windows 8 32 bit 64 bit Editions Microsoft Windows 7 32 bit 64 bit Editions Windows Server 2008 32 bit 64 bit Editions Windows Vista 32 bit 64 bit Editions Windows XP 32 bit 64 bit Editions PCI Express x1, x4, x8 x16 lane slots
Approvals	Other Approvals Microsoft Approvals	AEO C-TPAT Microsoft Certified Gold Partner WEEE RoHS EMC: CE TAA Windows 7 32 bit 64 bit Editions Windows Server 2008 32 bit 64 bit editions Windows Vista 32 bit 64 bit editions Windows Server 2003 32 bit 64 bit editions Windows XP 32 bit 64 bit editions
General	PCB Layers Power Consumption Weight Size	4 awaiting 0.653 kg 170(l) x 240(w) x 60(h) mm
Box Content	Packaging Card Cables	Installation CD including manual, Microsoft signed drivers & utilities PCIe 4 + 1xRS232 + 1xLPT Printer Port 4 port cable 44 way D to 4x9 Pin Male D + 1 port 9 Pin Male D on Fly lead + 25 Pin Female D Connector on Fly Lead
Product Support  	Warranty Support	Lifetime (online registration required) Lifetime Web, Email and Phone Support from fully qualified, friendly staff who work in and alongside the Product Development Team
Additional  	OEM option Made In Customisable	Available for bulk buy OEM Manufactured in the UK by Brainboxes Winner 2005 European Electronics Industry Awards "Manufacturer of the Year" Brainboxes operate a "Perfect Fit Custom Design" policy for volume users. More Info: sales@brainboxes.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Brainboxes:

PX-306