


RoHS Compliant

PX-801

LP PCIe 1 + 1xRS232 POS 1A SATA

"SERIAL CARDS ENGINEERED TO EXCEED EXPECTATIONS"



Features

- 1 + 1 port RS232
- PCI Express x1, x4, x8 x16 lane slots socket size
- 128 Byte Tx and 128 Byte Rx FIFOs
- Up to 921,600 Baud
- DB9 connector (9 Pin Male)
- Drivers for all popular operating systems
- Sample Programs, Test & Terminal software
- Lifetime Support
- Lifetime Warranty (registration required)

Options



PX-801:
LP PCIe 1 + 1xRS232 POS
1A SATA

Description


Low profile PCI Express Card providing two powered RS232 serial ports. Board gives first serial port on the bracket, with a second serial port on a fly lead. Data transfer rates up to 921,600 baud rates and the 128 byte deep transmit and 128 byte receive FIFOs, coupled with 1Mbit/s line drivers deliver uncompromising performance on your PC. Up to 1 Amp selectable power provided through pins 1 and 9 to attached peripherals. The extra power necessary is supplied to the PCI express card directly from the PC power supply unit through a Serial ATA SATA power connector: a neat, clean and green solution. Drivers for Windows 32 bit and 64 bit Operating Systems including Windows 2000, XP, Server 2003, Vista, Server 2008, Windows 7 and Windows 8.

Software

Microsoft signed drivers (easy installation & robust operation) for:

- Windows 7 32 bit 64 bit Editions
- Windows Server 2008 32 bit 64 bit Editions
- Windows Vista 32 bit 64 bit editions
- Windows Server 2003 32 bit 64 bit Editions

As well as: full product documentation, a thorough troubleshooting guide and terminal software. Detailed sample source code for many popular programming languages. Further OS support on next page.




ORDER

Description

LP PCIe 1 + 1xRS232 POS 1A SATA

Code

PX-801



LP PCIe 1 + 1xRS232 POS 1A SATA

PX-801: Full Specification

Port 	Ports Connector FIFO size Operating Distance Cable	1 + 1 x RS232 DB9 Connector - 9 Pin Male 128 RX FIFO + 128 TX FIFO EIA - RS232 Standard 1 port RS232 on fly lead
Port Settings 	Baud Rate Data Bits Parity Stop Bits Flow Control Tx/Rx Modes	921,600 5,6,7 or 8 Odd, Even, None, Mark or Space 1, 1.5 or 2 RTS/CTS, DSR/DTR, XON/XOFF Point to Point
Interface 	OS Compatibility BUS	Microsoft Windows 8 32 bit 64 bit Editions Microsoft Windows 7 32 bit 64 bit Editions Windows Server 2008 32 bit 64 bit Editions Windows Vista 32 bit 64 bit Editions Windows Server 2003 32 bit 64 bit Editions PCI Express x1, x4, x8 x16 lane slots
Approvals	Other Approvals Microsoft Approvals	AEO C-TPAT Microsoft Certified Gold Partner WEEE RoHS EMC: CE TAA Windows 7 32 bit 64 bit Editions Windows Server 2008 32 bit 64 bit editions Windows Vista 32 bit 64 bit editions Windows Server 2003 32 bit 64 bit editions Windows XP 32 bit 64 bit editions
General	PCB Layers Power Consumption Weight Size	4 400mA @ 3.3V 0.056 kg 133l x 18w x 80h mm
Box Content	Packaging Card	Installation CD including manual, Microsoft signed drivers & utilities LP PCIe 1 + 1xRS232 POS 1A SATA 1 port RS232 on fly lead
Product Support 	Warranty Support	Lifetime (online registration required) Lifetime Web, Email and Phone Support from fully qualified, friendly staff who work in and alongside the Product Development Team
Additional 	OEM option Made In Customisable	Available for bulk buy OEM Manufactured in the UK by Brainboxes Winner 2005 European Electronics Industry Awards "Manufacturer of the Year" Brainboxes operate a "Perfect Fit Custom Design" policy for volume users. More Info: sales@brainboxes.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Brainboxes:

PX-801