

**RoHS Compliant**

# UC-734/UC-253

## uPCI 2xRS232

"SERIAL CARDS ENGINEERED TO EXCEED EXPECTATIONS"



### Description

Universal PCI providing two RS232 serial ports on cable. Data transfer rates up to 115,200 baud rates and the 128 byte deep transmit and 128 byte receive FIFOs, coupled with 1Mbit/s line drivers deliver uncompromising performance on your PC. Includes drivers for all Windows 32 bit and 64 bit Operating Systems, including Windows 7.

With Brainboxes industry renowned Lifetime Warranty and Lifetime Support!

### Features

- 2 port RS232
- PCI 3.0
- 128 Byte Tx and 128 Byte Rx FIFOs
- Up to 115,200 Baud
- DB9 connector (9 Pin Male)
- Drivers for all popular operating systems
- Sample Programs, Test & Terminal software
- Lifetime Support
- Lifetime Warranty (registration required)

### Software

Microsoft signed drivers (easy installation & robust operation) for:

- Windows 7 32 bit 64 bit Editions
- Windows Server 2008 32 bit 64 bit Editions
- Windows Vista 32 bit 64 bit editions
- Windows Server 2003 32 bit 64 bit Editions



As well as: full product documentation, a thorough troubleshooting guide and terminal software. Detailed sample source code for many popular programming languages. Further OS support on next page.

### Options



UC-734:  
uPCI 2xRS232

UC-253  
LP uPCI 2xRS232



### ORDER

Description

uPCI 2xRS232

LP uPCI 2xRS232

Code

UC-734

UC-253



## uPCI 2xRS232

### UC-734/UC-253 Full Specification

<p><b>Port</b></p> <table border="1"> <tr><td>Pin 1</td><td>DCD</td></tr> <tr><td>Pin 2</td><td>RXD</td></tr> <tr><td>Pin 3</td><td>TXD</td></tr> <tr><td>Pin 4</td><td>DTR</td></tr> <tr><td>Pin 5</td><td>GND</td></tr> <tr><td>Pin 6</td><td>DSR</td></tr> <tr><td>Pin 7</td><td>RTS</td></tr> <tr><td>Pin 8</td><td>CTS</td></tr> <tr><td>Pin 9</td><td>RI</td></tr> </table> <p>RS232 Pinout (9 Pin Male)</p>	Pin 1	DCD	Pin 2	RXD	Pin 3	TXD	Pin 4	DTR	Pin 5	GND	Pin 6	DSR	Pin 7	RTS	Pin 8	CTS	Pin 9	RI	<p>Ports</p> <p>Connector</p> <p>FIFO size</p> <p>Operating Distance</p> <p>Cable</p>	<p>2 x RS232</p> <p>DB9 Connector - 9 Pin Male</p> <p>128 RX FIFO + 128 TX FIFO</p> <p>EIA - RS232 Standard</p> <p>2 Port Cable: DB9 connector 9 Pin Male</p>
Pin 1	DCD																			
Pin 2	RXD																			
Pin 3	TXD																			
Pin 4	DTR																			
Pin 5	GND																			
Pin 6	DSR																			
Pin 7	RTS																			
Pin 8	CTS																			
Pin 9	RI																			
<p><b>Port Settings</b></p> <p>115,200 ▶▶▶▶ baud</p>	<p>Baud Rate</p> <p>Data Bits</p> <p>Parity</p> <p>Stop Bits</p> <p>Flow Control</p> <p>Tx/Rx Modes</p>	<p>115,200</p> <p>5,6,7 or 8</p> <p>Odd, Even, None, Mark or Space</p> <p>1, 1.5 or 2</p> <p>Point to Point</p>																		
<p><b>Interface</b></p>	<p>OS Compatibility</p> <p>BUS</p>	<p>Microsoft Windows 7 32 bit 64 bit Editions Windows Server 2008 32 bit 64 bit Editions Windows Vista 32 bit 64 bit Editions Windows Server 2003 32 bit 64 bit Editions Windows XP 32 bit 64 bit Editions Microsoft Windows 2000 DOS</p> <p>PCI : Universal PCI is fully compatible with both 3.3Volt and 5Volt PCI slots.</p>																		
<p><b>Approvals</b></p>	<p>Industry Approvals</p> <p>Microsoft Approvals</p>	<p>AEO C-TPAT C-Tick Microsoft Certified Gold Partner WEEE RoHS EMC: CE TAA</p> <p>Windows 7 32 bit 64 bit Editions Windows Server 2008 32 bit 64 bit editions Windows Vista 32 bit 64 bit editions Windows Server 2003 32 bit 64 bit editions Windows XP 32 bit 64 bit editions</p>																		
<p><b>General</b></p>	<p>PCB Layers</p> <p>Power Consumption</p> <p>Weight</p> <p>Size</p>	<p>4</p> <p>260mA @ 5V / 30mA @ 12V</p> <p>0.067 kg</p> <p>132l x 18w x 120h mm</p>																		
<p><b>Box Content</b></p>	<p>Packaging</p> <p>Card</p>	<p>Installation CD including manual, Microsoft signed drivers &amp; utilities</p> <p>uPCI 2xRS232</p> <p>2 Port Cable: DB9 connector 9 Pin Male</p>																		
<p><b>Product Support</b></p>	<p>Warranty</p> <p>Support</p>	<p>Lifetime (online registration required)</p> <p>Lifetime Web, Email and Phone Support from fully qualified, friendly staff who work in and alongside the Product Development Team</p>																		
<p><b>Additional</b></p>	<p>OEM option</p> <p>Made In</p> <p>Customisable</p>	<p>Available for bulk buy OEM</p> <p>Manufactured in the UK by Brainboxes Winner 2005 European Electronics Industry Awards "Manufacturer of the Year"</p> <p>Brainboxes operate a "Perfect Fit Custom Design" policy for volume users. More Info: <a href="mailto:sales@brainboxes.com">sales@brainboxes.com</a></p>																		

Other PCI Cards: 1xRS232 | 2xRS232 | 4xRS232 | 8xRS232 | 1xRS422/485 | 2xRS422/485 | 4xRS422/485

Other Brainboxes Ranges: PCI Express | Bluetooth Serial Adapter | Ethernet to Serial Adapter | PCMCIA Serial Card | ExpressCard Serial Adapter | USB to Serial

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Brainboxes:](#)

[UC-734](#)