

# US-320

## US-320 - Small Profile USB 1 Port RS422/485

- Our smallest form factor USB to Serial
- High retention USB connector for an unshakeable connection
- Comes with 0.5m USB cable
- Works where many other USB to Serial devices do not
- Industrial Specification: IP-50  
-40° C to +80° C / -40° F to +176° F



### Ultra small USB to serial adapter suitable for any environment

Have confidence, this product will match whatever baud rate your equipment needs without data loss. Includes large 512 Byte TxD and RxD FIFOs supporting high data throughput at high baud rates. Works across the full spectrum of baud rates up to 921,600 including standard and arbitrary values.

We provide our own software drivers - eliminating many common problems with USB to Serial - giving you have a reliable, stable, native com port solution.

*"I have tried many off the shelf USB to Serial adapters. Some break easily, others only work some of the time. Brainboxes installed in seconds and could communicate with anything I threw at it, I would recommend this device to anyone."*

*Colin Young, Nutek Europe*



Drivers for all popular operating systems including latest Windows

The high retention USB connection requires a minimum withdrawal requirement of 15N (thats a force of 1.5Kg or 3.4lbs). Connectors have orange color-coded insulator to differentiate from standard USB connectors. The connection is so strong that the port is capable of taking the weight of a bottle of champagne.



# US-320 - Small Profile USB 1 Port RS422/485

### Housing and connectors

- IP-50 rated non-conducting polyamide case
- DB9 Connector - 9 Pin Male
- High Retention USB Connector
- Wall mounting screw recess

### Environmental

- Operating Temperature -40 °C to +80 °C / -40 °F to +176 °F

### Power Supply

- Power Consumption 50mA @ 5V
- Power Supply input +5V through USB cable (supplied)




### Port Settings - RS422/485

- Baud Rate From 110 - 1 MegaBaud - Any custom Baud rate accepted
- Data Bits 5,6,7 or 8
- Parity Odd, Even, None, Mark or Space
- Stop Bits 1 or 2
- Flow Control RTS/CTS, XON/XOFF
- Tx/Rx Modes Full Duplex, Half Duplex Autogating

### RS422/485



Pin 1	TXD-
Pin 2	TXD+
Pin 3	RTS-
Pin 4	RTS+
Pin 5	GND
Pin 6	RXD-
Pin 7	RXD+
Pin 8	CTS
Pin 9	CTS+

RS422/485 Pinout (9 Pin)



IP-50 rated non-conducting case

Wall mounting option



### Lifetime Warranty and Support:

We can help with every aspect of your project, from getting you up and running to custom application.



### Optional: US-063 USB Type A Plug to Type B Plug 1000mm



1m cable available: US-063

Brainboxes have additional and alternative length cables available that are compatible with this product

### Packaging Information

- Packaging Installation CD including manual, Microsoft signed drivers & utilities, Quick Start Guide
- Packaged Weight 0.155 kg, 5.47 ounces
- Packaged Dims 160x135x45 mm, 6.3x5.3x1.8 inches
- GTIN Universal Code 837324003673

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Brainboxes:

US-320