



Non-Contact Voltage Testers



FEATURES	NCVT-1	NCVT-2P	NCVT-3P	NCVT-4IR	NCVT-5A	NCVT-6
Drop Protection	6.6' (2 m)	6.6' (2 m)	6.6' (2 m)	6.6' (2 m)	9.8' (3 m)	6.6' (2 m)
Ingress Protection	IP40	IP54	IP67	IP54	—	IP40
Safety and Standards	CAT IV 1000V, CE	CAT IV 1000V, CE	CAT IV 1000V, CE	CAT IV 1000V, CE	CAT IV 1000V	CAT IV 1000V, CE
Voltage	50-1000V AC	Mode 1: 12-1000V AC Mode 2: 70-1000V AC	Mode 1: 12-1000V AC Mode 2: 70-1000V AC	12-1000V AC	Mode 1: 12-1000V AC Mode 2: 70-1000V AC	12-1000V AC
Frequency Range	50-500Hz	50-500Hz	50-500Hz	50-500Hz	50-500Hz	50-500Hz
Audible and Visual Alarms	●	●	●	●	●	●
Auto-Power Off	●	●	●	●	●	●
Temperature	—	—	—	-22° – 482°F (-30° – 250°C)	—	—
Laser	—	—	—	Class 2	Class 3a	Class 2
Flashlight	—	—	●	—	—	—
Distance Measuring	—	—	—	—	—	●
LCD Display	—	—	—	Backlight	—	Reverse Contrast
Pocket Clip	●	●	●	●	●	●
Batteries Included	2 x AAA	2 x AAA	2 x AAA	2 x AAA	2 x AAA	2 x AAA
Overall Length	5.50" (139.7 mm)	5.83" (148.0 mm)	5.83" (148.0 mm)	6.25" (158.8 mm)	6.00" (152.4 mm)	6.45" (164 mm)



Specifications subject to change.

MKT031720 Rev 03/20 A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Klein Tools:

[NCVT2P](#) [NCVT2PKIT](#) [NCVT3P](#)