



Non-Contact Voltage Testers



FEATURES	NCVT-1P	NCVT-2P	NCVT-3P	NCVT-4IR	NCVT-5A	NCVT-6
Drop Protection	6.6' (2 m)	6.6' (2 m)	6.6' (2 m)	6.6' (2 m)	9.8' (3 m)	6.6' (2 m)
Ingress Protection	IP40	IP54	IP67	IP54	—	IP40
Safety and Standards	CAT IV 1000V, CE UKCA	CAT IV 1000V, CE UKCA	CAT IV 1000V, CE UKCA	CAT IV 1000V, CE UKCA	CAT IV 1000V	CAT IV 1000V, CE UKCA
Voltage	50-1000V AC	Range 1: 12-1000V AC Range 2: 70-1000V AC	Range 1: 12-1000V AC Range 2: 70-1000V AC	12-1000V AC	Range 1: 12-1000V AC Range 2: 70-1000V AC	12-1000V AC
Frequency Range	50-500Hz	50-500Hz	50-500Hz	50-500Hz	50-500Hz	50-500Hz
Audible and Visual Alarms	●	●	●	●	●	●
Auto-Power Off	●	●	●	●	●	●
Temperature	—	—	—	-22° – 482°F (-30° – 250°C)	—	—
Laser	—	—	—	Class 2	Class 3a	Class 2
Flashlight	—	—	●	—	—	—
Distance Measuring	—	—	—	—	—	●
LCD Display	—	—	—	Backlight	—	Reverse Contrast
Pocket Clip	●	●	●	●	●	●
Batteries Included	2 x AAA	2 x AAA	2 x AAA	2 x AAA	2 x AAA	2 x AAA
Overall Length	5.50" (139.7 mm)	5.83" (148.0 mm)	5.83" (148.0 mm)	6.25" (158.8 mm)	6.00" (152.4 mm)	6.45" (164 mm)



Specifications subject to change.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Klein Tools:

[NCVT2P](#) [NCVT2PKIT](#) [NCVT3P](#) [NCVT1P](#) [69355](#)