


INSULATION RESISTANCE TESTER

ET600

TEST UP TO 4000M Ω

AT

125V, 250V, 500V, and 1000V DC



CAT IV
600V

CAT III
1000V

KLEIN TOOLS



INSULATION RESISTANCE TESTER ET600

The ET600 is a multi-function Megohmmeter capable of producing 125V, 250V, 500V, and 1000V test voltages for insulation resistance measurements up to 4000MΩ. Convenient lock function for hands free operation, and dual-function backlit display to monitor process.



Measurement	ET600
Test Voltages	125V, 250V, 500V, 1000V
Insulation Resistance	4000MΩ
Test Lock	●
Live Circuit Detection	●
AC/DC Voltage	1000V
Resistance	4kΩ
True RMS	●
Audible Continuity	●
Backlight	●
Auto-Ranging	●
Auto-Zero	●
Data Hold	●
Max/Min Value	●
Auto Power-Off	●
LCD Display Count	4000
Bar Graph	●
Over-Range Indication	●
Durability	
Safety Rating	CAT IV 600V CAT III 1000V



Stand For Hands Free Operation



Includes:

- Owner's Manual
- Carrying Case
- Right Angle Test Leads
- Heavy-duty Alligator Test Leads
- 6 x AA Batteries

Cat. No.	UPC# 0-92644+	Description	Dimensions
ET600	69242-0	Insulation Resistance Tester	7.93" L x 3.59" W x 2.32" H (210.5 x 91.2 x 58.9 mm)
Accessories and Replacement Parts			
69417	69417-2	Magnetic Hanger (Clips securely into back of ET600)	
69410	69410-3	Replacement Right Angle Test Lead Set (One pair of universal test leads and one set of alligator clips)	
69420	69295-6	Replacement Heavy Duty Alligator Test Leads (One pair of heavy-duty test leads)	

Visit www.kleintools.com for safety warnings. Failure to follow all instructions and warnings may result in personal injury.

See our complete line of **Test & Measurement products**
www.kleintools.com



© 2019 Klein Tools, Inc.
Lincolnshire, IL 60069-1418
82826 Rev. 10/19 A



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Klein Tools:](#)

[ET600](#)