

SLIM-TIP INSULATED SCREWDRIVERS

Easily access tight spaces

 1000V

3/16" (5 mm)


1/4" (6 mm)


#1


#2


#1


#2




Meets or exceeds ASTM F1505-16 and IEC 60900:2018



SLIM-TIP INSULATED SCREWDRIVERS

Slim profile tips allow for greater access into terminal blocks, slim-style breakers, or other tight spaces near energized sources. A bright orange coating of insulation protects from electrical shock, as well as being flame and impact resistant. These screwdrivers come in different tip types and lengths, making them a must-have for any electrician's tool bag.

Slim tips for greater access

1000V-rated orange impact & flame-resistant insulation provides protection from electrical shock

Meets or exceeds ASTM F1505-16 and IEC 60900:2018

 1000V

Cushion-Grip handle for greater torque and comfort

Tip-Ident™ quickly identifies screwdriver tip type

Slim-tip blade for easier access to terminal blocks and other tight spaces

MAGNETIZER

Mag/DeMag tool magnetizes or demagnetizes these insulated drivers.



USA

Cat. No.	UPC 0-92644+	Tip	Type	Shank	Blade Length	Overall Length	SETS			
							33732INS	33734INS	33736INS	
							32810-7	32811-4	33706-2	
INDIVIDUAL SCREWDRIVERS	6924INS	32812-1	1/4" (6 mm)		Round	4" (10 cm)	8.31" (21 cm)			
	6926INS	32820-6				6" (15 cm)	10.31" (26 cm)			
	6916INS	32814-5				6" (15 cm)	10.31" (26 cm)			
	6956INS	32825-1	#1			6" (15 cm)	10.31" (26 cm)			
	6934INS	32813-8	#2			4" (10 cm)	8.31" (21 cm)			
	6936INS	32821-3				6" (15 cm)	10.31" (26 cm)			
	6984INS	32823-7	#1			4" (10 cm)	8.31" (21 cm)			
	6986INS	32824-4				6" (15 cm)	10.31" (26 cm)			
	6944INS	32822-0	#2			4" (10 cm)	8.31" (21 cm)			
	6946INS	32815-2				6" (15 cm)	10.31" (26 cm)			
	MAG2	324468	Magnetizer / Demagnetizer							

Visit www.kleintools.com for warnings and instructions.

See our complete line of **Drivers and Accessories**
www.kleintools.com



© 2021 Klein Tools, Inc.
Lincolnshire, IL 60069
82903 Rev. 06/21 B

For Professionals
SINCE 1857™



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Klein Tools:

[33736INS](#) [6926INS](#) [6936INS](#) [6944INS](#) [6984INS](#) [6986INS](#)