



CABLE MANAGEMENT SOLUTIONS

Durable and reusable cable organizers
for the home, office or job site



**KLEIN
TOOLS®**



CABLE MANAGEMENT SOLUTIONS



450-320 (1.25" diameter, 3' long)
450-330 (1.75" diameter, 3' long)

Cable & Wire Management Sleeves

- Made of durable reusable material with hook and loop seal
- Adjustable hook and loop design offers a strong seal at any diameter
- Included back stitch and strong glue allows 3' sleeve to be cut to any length



450-600

Hook & Loop Cinch Straps, 6/8/14" Multi-Pack

- Durable loops run the entire length of the strap to cinch at any point for added flexibility
- Three lengths offer a wide range of uses for cables, wires other items to be bundled
- Premium metal loop to tighten hook and loop material
- Pack includes 2 of each length (6", 8" and 14")



450-700



Stretch Cable Tie Roll

- Self-locking at any diameter
- 75-feet that can be easily cut to length
- Exclusive design features optional screw mounting holes
- Standalone or mountable
- Sold in convenient dispenser box



450-410



450-400

Cable Clips

- Available in 10 packs of either single or triple cable clips
- Quality 3M® adhesive backing holds up to 194° F (90° C)
- Mount to a variety of surfaces
- Includes screws for optional permanent mounting



3M is a registered trademark of 3M Company.

Selection Guide

Cat. No.	UPC# 0-92644+	Description	Quantity
450-320	58363-6	Cable Sleeves, 1.25" Wide, 3' Long	2
450-330	58364-3	Cable Sleeves, 1.75" Wide, 3' Long	2
450-600	58365-0	Cinch Straps, 6/8/14" Multi-Pack	6 (2/each)
450-400	58357-5	Cable Mounting Clips, Single Hole	10
450-410	58358-2	Cable Mounting Clips, Triple Hole	10
450-700	58371-1	Stretch Cable Tie Roll	75-feet

⚠ Visit www.kleintools.com for warnings and instructions.



See our complete line of **Cable Management Options**
www.kleintools.com



© 2021 Klein Tools, Inc.
Lincolnshire, IL 60069
82955 Rev. 07/21 B

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Klein Tools:](#)

[450-700](#)