

Heavy-Duty Ratcheting Bolt Cutter

One smooth, easy cut
does it all.



**KLEIN
TOOLS®** 
For Professionals... Since 1857™

EASY AS



OPEN

movable handle to full extension to open cutting jaws



SNAP

pull cable between cutting jaws



CUT

cut cable using ratcheting handle

The Heavy-Duty Ratcheting Bolt Cutter easily slices through guy strand in just one cut. A smooth ratchet mechanism makes this bolt cutter the easiest to use on the market.



Spring-loaded cable retention hook

- Snaps onto the cable in one hands free motion.
- Prevents individual steel strands from slipping out of the cutting jaws.

- Cuts 1/4" - 1/2" (6.35 mm - 12.7 mm) **utility-grade guy strand**
- Cuts up to 3/8" (9.5 mm) **EHS**

Lockplate

prevents jaw bolts from loosening or turning, keeping jaws in correct alignment.

Long handles

for high leverage.

Cat. No.	UPC 092644+	Cutting Capacity	Up to HRC	Overall Length
63RBCHD	63067-5	1/4" - 1/2" (12.7 mm) Guy Strand up to 3/8" (9.5 mm) EHS	Rockwell C31 Rockwell C42	31" (78 cm)

*As defined by ASTM A475-98, 1/2" utility grade 7-strand guy strand has minimum breaking strength of 25,000 lbs (11,339.81 kg). 3/8" EHS 7-strand has minimum breaking strength of 15,400 lbs (6,985 kg).

KLEIN TOOLS
EST. 1857
For Professionals... Since 1857™

See our complete line of Utility products

www.kleintools.com



© 2016 Klein Tools, Inc.
Lincolnshire, IL 60069-1418
96403 Rev. 03/16 B

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Klein Tools:](#)

[63RBCHD](#)