

LEVELS

Patent Pending

**MAGNET
TRACK**

ULTRA
POWERFUL
Rare-Earth Magnets



**KLEIN
TOOLS**
For Professionals... Since 1857™



PROFESSIONAL-GRADE BILLET ALUMINUM LEVELS

Precision machined for high-accuracy leveling

Prevent dog-legs in conduit bends

Unique 3-point attachment to securely hold to conduit



**ACCU-BEND™
4-VIAL LEVEL**
935AB4V

**ACCU-BEND™
1-VIAL LEVEL**
(does not include magnets)
935AB1V

**HIGH-VISIBILITY
ORANGE**
won't get lost on conduit

Patent Pending

**MAGNET
TRACK**

Permanently locks magnets to levels



Top V-Groove fits contour of pipe



**BILLET ALUMINUM
TORPEDO LEVEL**
935RB

Tapered nose easily slides into pockets and fits in tighter spaces

**ULTRA
POWERFUL**
Rare-Earth Magnets

EASY-TO-READ
vials with top-view windows

**SUPER
BRIGHT
HIGH-DEFINITION
LED VIALS**



**LIGHTED BILLET
TORPEDO LEVEL**
935RBLT



**LIGHTS
UP!**



ALUMINUM TORPEDO LEVEL

935R

- Tough aluminum frame
- Ultra powerful rare-earth magnets with locking track
- High-visibility orange body

TORPEDO LEVEL


935

- High-visibility orange body
- Strip magnet



Levels available in 6-pack
COUNTER DISPLAYS!*

*935 not available in a display

	Cat No.	UPC 0-92644+	Description	Vials	Magnet	Length	Weight
	935	93500-8	Torpedo Level	Level, 90°, 45°	Strip Magnet	9" (229 mm)	.26 lbs. (118 g)
	935R	93501-5	Aluminum Torpedo Level	Level, 90°, 45°	Ultra Powerful Rare-Earth	9" (229 mm)	.55 lbs. (249 g)
	935RB	93502-2	Billet Aluminum Torpedo Level	Level, 90°, 45°, 30°	Ultra Powerful Rare-Earth	8" (203 mm)	.45 lbs. (204 g)
	935RBLT	93503-9	Lighted Billet Aluminum Torpedo Level	Level, 90°, 45°	Ultra Powerful Rare-Earth	9" (229 mm)	.66 lbs. (299 g)
	935AB1V	93506-0	Accu-Bend™ 1-Vial Level	90°	N/A	2.5" (64 mm)	.15 lbs. (68 g)
	935AB4V	93507-7	Accu-Bend™ 4-Vial Level	Level, 90°, 45°, 30°	Ultra Powerful Rare-Earth	6.25" (159 mm)	.37 lbs. (168 g)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Klein Tools:

[935AB1V](#) [935AB4V](#) [935RBLT](#) [935R](#) [935RB](#) [935](#)