

DIGITAL POCKET THERMOMETER

ET05



-40° - 482° F
-40° - 250° C



CE

KLEIN TOOLS
For Professionals... Since 1857™



DIGITAL POCKET THERMOMETER

ET05

HVAC\R

Rugged, portable design makes the **ET05** the perfect choice for HVAC professionals.

- User selectable Fahrenheit and Celsius temperature measurements
- Range -40 to 482° F (-40 to 250° C) with 0.1 degree resolution
- Lightweight, compact tool with pocket clip provides easy storage and quick access
- Auto-power off after 15 minutes conserves battery life



°F/°C Select Button
toggles between Fahrenheit (°F) and Celsius (°C)

Backlit LCD Display
for easy viewing in low light

Protective Sheath/Handle
open sheath provides stable ambient air measurement; can be used as a handle for extended reach



3" Stainless Steel Probe
FDA GRAS-compliant

Power On/Off Button

HOLD/MAX/MIN/AVG Button
to capture maximum, minimum and average values

Pocket Clip
also doubles as battery compartment for the device



Thermometer is NOT intended for use on people or animals.



Cat. No.	UPC# 0-92644+	Batteries	Height	Width	Depth	Weight (oz.)
ET05	69060-0	2x LR44	6.5" (165 mm)	1.08" (27 mm)	0.96" (24 mm)	1.3 (37 g)

KLEIN TOOLS
For Professionals... Since 1857™

See our complete line of Test & Measure and HVAC products

www.kleintools.com

Patent Pending



© 2017 Klein Tools, Inc.
Lincolnshire, IL 60069-1418
96505 Rev. 06/17 B

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Klein Tools:](#)

[ET05](#)