

FLEXIBLE AC CURRENT CLAMP METER

CL150



3000A ~

True RMS
Measurement
Technology



**KLEIN
TOOLS**





FLEXIBLE AC CURRENT CLAMP METER

This convenient, stand-alone meter features an 18" flexible clamp that allows access into panels and hard to reach areas (bundled wires, awkward conductors, and PLC cabinets).



3000A ~

18" Flexible Clamp

RADIUS MEASUREMENTS

r1. 1.38" (35 mm):
1% error
r2. 2" (50 mm):
1.5% error
r3. 2.38" (60 mm):
2.0% error



3000 Count LCD Display

MAX/MIN Button

Power Button

Coil Lock Clamp

Low Battery Indicator

HOLD/Backlight Button

- True RMS CAT IV 600V, CAT III 1000V meter
- Auto-ranging with direct readout from 0.1 to 3000A
- Auto-power off after 15 minutes of non-usage conserves battery life

Measurement		CL150
AC Current		3000A
True RMS		•
Backlight		•
Auto-Ranging		•
Data Hold		•
Max/Min Value		•
Auto Power-Off		15 Min.
LCD Display Count		3000
Durability		
Drop Protection		6.6 ft. (2 m)
Safety Rating		CAT III 1000V CAT IV 600V

Includes:

- Owner's Manual
- Storage Pouch,
- 2 x AAA Batteries



NOTE: There are no user-serviceable parts inside meter.

Cat. No.	UPC# 0-92644+	Batteries	Height	Width	Depth	Weight (oz.)
CL150	69099-0	2 x AAA	10.5" (266 mm)	4.12" (104 mm)	1.06" (27 mm)	15.0 (425 g)

See our complete line of Test & Measure and HVAC products

www.kleintools.com



© 2018 Klein Tools, Inc.
Lincolnshire, IL 60069-1418
96534 Rev. 03/18 A



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Klein Tools:](#)

[CL150](#)