

MAGNETIC POCKET THERMOMETER

ET10



-40° - 572° F
-40° - 300° C



CE

KLEIN TOOLS 
For Professionals... Since 1857™

MAGNETIC POCKET THERMOMETER

ET10

HVAC/R



Rugged, portable design **with magnet** makes the **ET10** a handy choice for HVAC professionals.

- User selectable Fahrenheit and Celsius temperature measurements
- Range -40° to 572° F (-40° TO 300° C)
- Lightweight, compact tool with pocket clip provides easy storage and quick access
- Auto power-off after 15 minutes conserves battery life



Batteries included.

Thermometer is NOT intended for use on people or animals.



Cat. No.	UPC# 0-92644+	Batteries	Height	Width	Depth	Weight (oz.)
ET10	69145-4	2x LR44	6.5" (165 mm)	1.26" (32 mm)	0.96" (24 mm)	1.5 (42.5 g)
Also available NON-MAGNETIC version:						
ET05	69060-0	2x LR44	6.5" (165 mm)	1.08" (27 mm)	0.96" (24 mm)	1.3 (37 g)

KLEIN TOOLS
For Professionals... Since 1857™

See our complete line of Test & Measure and HVAC products

www.kleintools.com

Patent Pending



© 2017 Klein Tools, Inc.
Lincolnshire, IL 60069-1418
96540 Rev.11/17 A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Klein Tools:](#)

[ET10](#)