

BORESCOPE SELECTION GUIDE



**ET17 Utility
Borescope**



**ET18 Plumber's
Borescope**



**ET19 Pro
Borescope**

Snake	9.8ft Nylon	5ft Armored	9.8ft Armored
Camera Resolution	1280x720p	1280x720p	1280x720p
Number of Lenses	Single	Single	Dual
Camera Head Size	5.5mm	5.5mm	5.5mm
Number of LED Lights	6	6	6
Screen Size	4.3"	4.3"	4.3"
Display Resolution	854x480p	854x480p	854x480p
Included Attachments	Hook, Magnet, Mirror	Hook, Magnet, Mirror	Hook, Magnet
IP - Camera Head	IP67	IP67	IP67
Internal Storage	2GB	2GB	2GB
Image/Video Transfer	USB-C	USB-C	USB-C/Wi-Fi
Photo Capture	●	●	●
Video Capture	●	●	●
Digital Zoom	Yes	Yes	Yes
Included	Borescope; 5.5mm Camera with 9.8' (3m) Snake; USB-C Cable; Camera Accessories: Magnet, Hook, Mirror; Carrying Case	Borescope; 5.5mm Camera with 5' (1.5m) Armored Snake, USB-C Cable; Camera Accessories: Magnet, Hook, Mirror; Carrying Case	Borescope; 5.5mm Camera with 9.8' (3m) Armored Snake; USB-C Cable; Camera Accessories: Magnet, Hook; Carrying Case
Battery Type	USB-C Rechargeable Lithium-Ion 2000 mAh, 7.4 Wh	USB-C Rechargeable Lithium-Ion 2000 mAh, 7.4 Wh	USB-C Rechargeable Lithium-Ion 2000 mAh, 7.4 Wh
Overall Height	1.51" (3.8 cm)	1.51" (3.8 cm)	1.51" (3.8 cm)
Overall Length	6.55" (16.6 cm)	6.55" (16.6 cm)	6.55" (16.6 cm)
Overall Width	3.19" (8.1 cm)	3.19" (8.1 cm)	3.19" (8.1 cm)
Weight	8.6 oz (244 g)	8.6 oz (244 g)	8.6 oz (244 g)
Certifications	CE and UKCA	CE and UKCA	CE and UKCA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Klein Tools:](#)

[ET18](#) [69464](#) [69473](#) [ET19](#)