

CL440 HVAC CLAMP METER

True RMS
Measurement
Technology

750V ~
600V =
600A ~
60M Ω

 -328° –
2462°F
-200° –
1350°C

CAT III CAT IV
750V 600V

**KLEIN
TOOLS** 

CL440 HVAC CLAMP METER

Klein Tools CL440 is an advanced HVAC clamp meter with auto-ranging true root mean square (TRMS) for maximum accuracy. The meter measures AC current and inrush via the clamp, AC/DC voltage, DC microamps, resistance, continuity, frequency, capacitance, and tests diodes via test-leads, and temperature via a thermocouple probe.

Includes:

- Right-angle Input Test Leads
- Push-on Alligator Clips
- K-Type Thermocouple
- Storage Pouch
- Instruction Manual
- 3 AAA Batteries



CAT IV 600V **CAT III 750V**

Measurement		CL440
True RMS	TRMS	●
AC Voltage		750V
DC Voltage		600V
AC Current		600A
Resistance		60MΩ
DC Millivolts		●
DC Microamps		●
Inrush Current		●
Non-Contact Voltage Testing	NCV	●
Audible Continuity		●
Backlight		●
Temperature		-328° – 2462°F (-200° – 1350°C)
Auto-Ranging	AUTO	●
Range Hold	RANGE	●
Data Hold	HOLD	●
Diode Test		●
Capacitance Test		●
Frequency/Duty Cycle	Hz%	●
Max/Min Value	MAX/MIN	●
Auto Power-Off	APO	●
LCD Display Count		6000
Durability		
Safety Rating		CAT IV 600V

For Professionals
SINCE 1857™



Cat. No.	UPC#	Description	Height	Length	Width	Weight
CL440	69335-9	HVAC Clamp Meter	1.57" (4.0 cm)	10.04" (25.5 cm)	3.77" (9.6 cm)	14.2 oz (40 g)

⚠ Visit www.kleintools.com for warnings and instructions.

See our complete line of **Test & Measurement Products**
www.kleintools.com



© 2021 Klein Tools, Inc.
Lincolnshire, IL 60069
MKT030821 Rev. 03/21 A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Klein Tools:](#)

[CL440](#)