




Extra-Wide Jaw

8" ADJUSTABLE WRENCH



**SAME
CAPACITY AS A
STANDARD 12" WRENCH**

For Professionals... Since 1857®

**KLEIN
TOOLS®**

Extra-Wide Jaw

D509-8

Adjustable Wrenches

- **Standard and metric sizes** marked for faster adjustment.
- Manufactured for superior **strength and durability.**
- **Wide handle** for comfortable use.
- **Unique design minimizes protruding jaw shank** for greater capacity in tight spaces.

Get More Work Done... Faster and Easier

The Klein Tools Adjustable Wrenches you've come to rely on are now even better! Improved features like an **etched inch/metric measurement scale** and a **non-protruding jaw shank** make these wrenches more efficient, especially in tight spaces. A unique **4-threaded knurl worm gear** helps balance these wrenches for smoother operation and allows the user to apply up to **30% more force.**



D509-8



Cat. No.	UPC + 0-92644	Description	Handle	Length	Capacity	Weight (lbs.)
NEW! D509-8	19003-2	8" extra-wide jaw adjustable wrench	plastic dipped – solid blue	8-1/2" (216 mm)	1-1/2" (38 mm)	0.77

Other Adjustable Wrenches with Improved Features

D506-4	67501-0	4" standard capacity adjustable wrench	plastic dipped – transparent red	4-5/8" (117 mm)	1/2" (13 mm)	0.13
D507-6	67525-6	6" high capacity adjustable wrench	plastic dipped – transparent red	6-1/2" (165 mm)	15/16" (24 mm)	0.27
D507-8	67528-7	8" high capacity adjustable wrench	plastic dipped – transparent red	8-1/4" (209 mm)	1-1/8" (28 mm)	0.62
D507-10	67531-7	10" high capacity adjustable wrench	plastic dipped – transparent red	10-1/4" (260 mm)	1-5/16" (33 mm)	1.00
D507-12	67534-8	12" high capacity adjustable wrench	plastic dipped – transparent red	12-3/8" (314 mm)	1-1/2" (38 mm)	1.24
507-6	67524-9	6" high capacity adjustable wrench	high-polish chrome	6-3/8" (162 mm)	15/16" (24 mm)	0.25
507-8	67527-0	8" high capacity adjustable wrench	high-polish chrome	8-1/8" (206 mm)	1-1/8" (28 mm)	0.51
507-10	67530-0	10" high capacity adjustable wrench	high-polish chrome	10-1/8" (257 mm)	1-5/16" (33 mm)	0.86
507-12	67533-1	12" high capacity adjustable wrench	high-polish chrome	12-1/4" (311 mm)	1-1/2" (38 mm)	1.32
506-15	67515-7	15" high capacity adjustable wrench	high-polish chrome	15-7/8" (403 mm)	1-11/16" (43 mm)	2.92
500-18	67018-3	18" standard capacity adjustable wrench	high-polish chrome	18-1/4" (463 mm)	2-1/16" (52 mm)	4.67
500-24	67021-3	24" standard capacity adjustable wrench	high-polish chrome	24" (610 mm)	2-1/2" (63 mm)	7.76

**KLEIN
TOOLS®**

See our complete line of Combination, Open End, Socket, Specialty and Ratcheting Box Wrenches

www.kleintools.com


© 2012 Klein Tools, Inc.
Lincolnshire, IL 60069-1418
Printed in U.S.A. 96161

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Klein Tools:](#)

[D509-8](#)