

DIGITAL MULTIMETERS



FEATURES	MM300	MM400	MM600	MM700
Durability				
Drop Protection	3.3 ft. (1 m)	3.3 ft. (1 m)	6.6 ft. (2 m)	6.6 ft. (2 m)
Ingress Protection	—	—	IP42	IP42
Safety	CAT III 600V	CAT III 600V	CAT IV 600V	CAT IV 600V
AC Voltage (Volts)	600V	600V	1000V	1000V
DC Voltage (Volts)	600V	600V	1000V	1000V
AC Current (Amps)	—	10A	10A	10A
DC Current (Amps)	10A	10A	10A	10A
Ohms (Resistance)	2MΩ	40MΩ	40MΩ	40MΩ
DC Millivolts	•	•	•	•
AC Milliamps	—	•	•	•
DC Milliamps	•	•	•	•
AC Microamps	—	•	•	•
DC Microamps	•	•	•	•
True RMS	—	—	—	•
Audible Continuity	•	•	•	•
Backlight	—	•	•	•
Temperature	—	0° – 1000°F (-18° – 538°C)	0° – 1000°F (-18° – 538°C)	0° – 1500°F (-18° – 816°C)
Low Impedance	—	—	—	•
Auto Ranging	—	•	•	•
Range Hold	—	•	•	•
Data Hold	•	•	•	•
Diode Test	•	•	•	•
Capacitance Test	—	200 μF	1000 μF	4000 μF
Frequency / Duty Cycle	—	1Hz – 50 KHz	1Hz – 500 KHz	1Hz – 500 KHz
Max / Min	—	•	•	•
Lead Warning	—	—	•	•
Bar Graph	—	—	—	•
Magnetic Mount	Available As Accessory	Available As Accessory	Available As Accessory	Available As Accessory
Auto-Power Off	—	•	•	•
Battery Test	•	—	—	—
LCD Display Count	2000	4000	4000	4000

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Klein Tools:](#)

[69149](#) [69149P](#)